

| ProTool | | | | | | | | | | | | | | | |
|-----------------------------|--------------|------------------------|-------------|-----------------|-----------------|-----------------|------------------|-------------|-------------|-------|---------------|------------------|----------------|------------------|----------------|
| product name | version | order number (e.g.) | STEP 7 V5.1 | | | | | STEP 7 V5.2 | | | | | STEP 7 V5.3 | | |
| | | | Win95 | Win98 SE | Win NT 4.0 | WinME | Win2000 Prof. | Win95 | Win98 SE | WinME | Win NT 4.0 | Win2000 Prof. | WinXP Prof. | Win2000 Prof. | WinXP Prof. |
| ProTool/Lite/Pro CS + RT | V6.0+SP 3 | 6AV6 582-2BX06-0DX0 | - | x ¹⁾ | x ¹⁾ | x ¹⁾ | x ¹⁾ | - | x | x | x | x | x | x | x |
| ProTool/Lite/Pro CS + RT | V6.0+SP 2 | 6AV6 582-2BX06-0CX0 | - | x ¹⁾ | x ¹⁾ | x ¹⁾ | x ¹⁾ | - | x | x | x | x | x | x | x |
| ProTool/Lite/Pro CS + RT | V5.2+SP 3 | 6AV6 582-2BX05-2CX0 | x | x | x | x | x | x | x | x | x | x | - | x | - |

| ProAgent | | | | | | | | | | | | | | | |
|---------------------|----------|------------------------|-------------|-----------------|-----------------|-----------------|------------------|-------------|-------------|-------|---------------|------------------|----------------|------------------|----------------|
| product name | version | order number (e.g.) | STEP 7 V5.1 | | | | | STEP 7 V5.2 | | | | | STEP 7 V5.3 | | |
| | | | Win95 | Win98 SE | Win NT 4.0 | WinME | Win2000 Prof. | Win95 | Win98 SE | WinME | Win NT 4.0 | Win2000 Prof. | WinXP Prof. | Win2000 Prof. | WinXP Prof. |
| ProAgent CS | V6.0+SP3 | 6AV6581-3BX06- 0DX0 | - | x ¹⁾ | x ¹⁾ | x ¹⁾ | x ¹⁾ | - | x | x | x | x | x | x | x |
| ProAgent RT | V6.0+SP3 | 6AV6582-2BX06- 0DX0 | - | - | x ¹⁾ | x ¹⁾ | x ¹⁾ | - | - | - | x | x | x | x | x |
| ProAgent CS | V6.0+SP2 | 6AV6 582-2BX06-0CX0 | - | x ¹⁾ | x ¹⁾ | x ¹⁾ | x ¹⁾ | - | x | x | x | x | x | x | x |
| ProAgent RT | V6.0+SP2 | 6AV6 582-2BX06-0CX0 | - | - | x ¹⁾ | x ¹⁾ | x ¹⁾ | - | - | - | x | x | x | x | x |
| ProAgent CS + RT | V5.2+SP3 | 6AV6 582-2BX05-2CX0 | x | x | x | x | x | x | x | x | x | x | - | x | - |

Description of characters:

- X := combination permitted
- := combination not permitted

¹⁾ STEP 7 V5.1 **SP4**