

C7 control system		integrated S7-300 CPU		integrated HMI-Panel
C7-626	6ES7626-1AG00-0AE3	CPU 315	6ES7315-1AF00-0AB0	OP25
	6ES7626-1AG01-0AE3	CPU 315	6ES7315-1AF01-0AB0	OP25
	6ES7626-1AG02-0AE3	CPU 315	6ES7315-1AF02-0AB0	OP25
C7-626/A	6ES7626-1CG00-0AE3	CPU 315	6ES7315-1AF00-0AB0	OP25
	6ES7626-1CG01-0AE3	CPU 315	6ES7315-1AF01-0AB0	OP25
	6ES7626-1CG02-0AE3	CPU 315	6ES7315-1AF02-0AB0	OP25
C7-626/P	6ES7626-1DG02-0AE3	CPU 315	6ES7315-1AF02-0AB0	OP25
	6ES7626-1DG03-0AE3	CPU 315	6ES7315-1AF03-0AB0	OP25
C7-626 DP	6ES7626-2AG00-0AE3	CPU 315-2DP	6ES7315-2AF00-0AB0	OP25
	6ES7626-2AG01-0AE3	CPU 315-2DP	6ES7315-2AF01-0AB0	OP25
	6ES7626-2AG02-0AE3	CPU 315-2DP	6ES7315-2AF02-0AB0	OP25
C7-626/P DP	6ES7626-2DG02-0AE3	CPU 315-2DP	6ES7315-2AF02-0AB0	OP25
	6ES7626-2DG03-0AE3	CPU 315-2DP	6ES7315-2AF03-0AB0	OP25
C7-633 DP	6ES7633-2BF00-0AE3	CPU 315-2DP	6ES7315-2AF02-0AB0	OP7
	6ES7633-2BF01-0AE3	CPU 315-2DP	6ES7315-2AF03-0AB0	OP7
	6ES7633-2BF02-0AE3	CPU 315-2DP	6ES7315-2AF03-0AB0	OP7
C7-633 P	6ES7633-1DF00-0AE3	CPU 315	6ES7315-1AF02-0AB0	OP7
	6ES7633-1DF01-0AE3	CPU 315	6ES7315-1AF03-0AB0	OP7
	6ES7633-1DF02-0AE3	CPU 315	6ES7315-1AF03-0AB0	OP7
C7-634 DP	6ES7634-2BF00-0AE3	CPU 315-2DP	6ES7315-2AF02-0AB0	OP17
	6ES7634-2BF01-0AE3	CPU 315-2DP	6ES7315-2AF03-0AB0	OP17
	6ES7634-2BF02-0AE3	CPU 315-2DP	6ES7315-2AF03-0AB0	OP17
C7-634 P	6ES7634-1DF00-0AE3	CPU 315	6ES7315-1AF02-0AB0	OP17
	6ES7634-1DF01-0AE3	CPU 315	6ES7315-1AF03-0AB0	OP17
	6ES7634-1DF02-0AE3	CPU 315	6ES7315-1AF03-0AB0	OP17
C7-613	6ES7613-1CA00-0AE3	CPU 313C	6ES7313-5BE00-0AB0	TD, 4zeilig
	6ES7613-1CA01-0AE3	CPU 313C	6ES7 313-5BE01-0AB0	TD, 4zeilig
C7-635 Touch	6ES7635-2EB00-0AE3	CPU 314C-2DP	6ES7314-6CF00-0AB0	TP170B monochrom
	6ES7635-2EB01-0AE3	CPU 314C-2DP	6ES7314-6CF01-0AB0	TP170B monochrom
C7-635 Key	6ES7635-2EC00-0AE3	CPU 314C-2DP	6ES7314-6CF00-0AB0	OP170B
	6ES7635-2EC01-0AE3	CPU 314C-2DP	6ES7314-6CF01-0AB0	OP170B
C7-636 Key	6ES7636-2EC00-0AE3	CPU 315-2DP	6ES7315-2AG10-0AB0	OP270 6"