

OP7, OP15C, OP17 character	OP7, OP15C, OP17 (russ.) character	OP3, OP5, OP15A with LCD character	OP15A-VF with VF-Display character	ANSI Code
Blank	Blank	Blank	Blank	32
!	!	!	!	33
“	“	“	“	34
#	#	#	#	35
\$	\$	\$	\$	36
%	%	%	%	37
&	&	&	&	38
'	'	'	'	39
((((40
))))	41
*	*	*	*	42
+	+	+	+	43
,	,	,	,	44
-	-	-	-	45
.	.	.	.	46
/	/	/	/	47
0	0	0	0	48
1	1	1	1	49
2	2	2	2	50
3	3	3	3	51
4	4	4	4	52
5	5	5	5	53
6	6	6	6	54
7	7	7	7	55
8	8	8	8	56
9	9	9	9	57
:	:	:	:	58
;	;	;	;	59
<	<	<	<	60
=	=	=	=	61
>	>	>	>	62
?	?	?	?	63
@ (Blank)	@ (Blank)	@ (Blank)	@ (Blank)	64
A	A	A	A	65
B	B	B	B	66
C	C	C	C	67
D	D	D	D	68
E	E	E	E	69
F	F	F	F	70
G	G	G	G	71
H	H	H	H	72
I	I	I	I	73
J	J	J	J	74
K	K	K	K	75
L	L	L	L	76
M	M	M	M	77

OP7, OP15C, OP17 character	OP7, OP15C, OP17 (russ.) character	OP3, OP5, OP15A with LCD character	OP15A-VF with VF-Display character	ANSI Code
N	N	N	N	78
O	O	O	O	79
P	P	P	P	80
Q	Q	Q	Q	81
R	R	R	R	82
S	S	S	S	83
T	T	T	T	84
U	U	U	U	85
V	V	V	V	86
W	W	W	W	87
X	X	X	X	88
Y	Y	Y	Y	89
Z	Z	Z	Z	90
[[[[91
\	\	\	\	92
]]]]	93
^	Ь	^	^	94
_	—	_	_	95
`	Ю	`	`	96
a	А	a	a	97
b	Б	b	b	98
c	Ц	c	c	99
d	Д	d	d	100
e	Е	e	e	101
f	Ф	f	f	102
g	Г	g	g	103
h	Х	h	h	104
i	И	i	i	105
j	Й	j	j	106
k	К	k	k	107
l	Л	l	l	108
m	М	m	m	109
n	Н	n	n	110
o	О	o	o	111
p	П	p	p	112
q	Я	q	q	113
r	Р	r	r	114
s	С	s	s	115
t	Т	t	t	116
u	У	u	u	117
v	Ж	v	v	118
w	В	w	w	119
x	Ь	x	x	120
y	Ы	y	y	121
z	З	z	z	122
{	Ш	{	{	123
	Э			124

OP7, OP15C, OP17 character	OP7, OP15C, OP17 (russ.) character	OP3, OP5, OP15A with LCD character	OP15A-VF with VF-Display character	ANSI Code
}	Ш	}	}	125
~	У	~	~	126
■	■	■	■	127
□	□	□	□	128
Ⓔ	Ⓔ	-	Ⓔ	129
┌	┌	-	-	130
f	f	-	f	131
▤	▤	-	-	132
▥	▥	-	-	133
▦	▦	-	-	134
		-	-	135
←	←	←	←	136
≡	≡	-	-	137
≡	≡	-	-	138
π	π	-	-	139
ϣ	ϣ	-	-	140
≡	≡	-	-	141
		-	-	142
┐	┐	-	-	143
┘	┘	-	-	144
┘	┘	-	-	145
┘	┘	-	-	146
┘	┘	-	-	147
┘	┘	-	-	148
•	•	-	-	149
↑	↑	↑ (D/E/F/I/S)	↑	150
↓	↓	↓ (D/E/F/I/S)	↓	151
→	→	→	→	152
—	—	—	—	153
+	+	-	-	154
⌈	⌈	-	-	155
⌈	⌈	-	-	156
⌈	⌈	-	-	157
⌈	⌈	-	-	158
⌈	⌈	-	-	159
π	π	-	-	160
i	i	-	-	161
ϕ	ϕ	-	ϕ	162
£	£	-	£	163
⌈	⌈	-	-	164
¥	¥	-	¥	165
=	=	-	-	166
≡	≡	-	-	167
≡	≡	-	-	168
		-	-	169
a	a	-	-	170

OP7, OP15C, OP17 character	OP7, OP15C, OP17 (russ.) character	OP3, OP5, OP15A with LCD character	OP15A-VF with VF-Display character	ANSI Code
«	«	-	-	171
¬	¬	-	-	172
⌈	⌈	-	-	173
⌊	⌊	-	-	174
ℓ	ℓ	-	-	175
°	°	°	°	176
±	±	-	±	177
²	²	-	-	178
ℓ	ℓ	-	-	179
ƒ	ƒ	-	-	180
μ	μ	μ	μ	181
∏	∏	-	-	182
·	·	·	-	183
∥	∥	-	-	184
≠	≠	-	-	185
°	°	-	-	186
»	»	-	-	187
¼	¼	-	¼	188
½	½	-	½	189
┘	┘	┘	-	190
¿	¿	¿(S)	¿(S)	191
┘	┘	┘	-	192
■	■	■	-	193
■	■	-	-	194
■	■	-	-	195
Ä	Ä	Ä (D)	Ä (D)	196
Å	Å	-	-	197
Æ	Æ	-	Æ	198
Ç	Ç	-	-	199
■	■	-	-	200
É	É	-	-	201
■	■	-	-	202
α	α	α	α	203
Γ	Γ	-	-	204
Π	Π	Π	-	205
Σ	Σ	Σ	-	206
σ	σ	σ	σ	207
τ	τ	-	-	208
Ñ	Ñ	-	-	209
Φ	Φ	-	-	210
Θ	Θ	Θ	-	211
Ω	Ω	Ω	Ω	212
ö	ö	-	-	213
Ö	Ö	Ö (D)	Ö (D)	214
∞	∞	∞	∞	215
∅	∅	-	-	216
ε	ε	ε	-	217

OP7, OP15C, OP17 character	OP7, OP15C, OP17 (russ.) character	OP3, OP5, OP15A with LCD character	OP15A-VF with VF-Display character	ANSI Code
∅	∅	-	-	218
≡	≡	-	-	219
Û	Û	Û (D)	Û (D)	220
≥	≥	-	≥	221
≤	≤	-	≤	222
β	β	β	β	223
à	à	à (F/I)	à (F/I)	224
á	á	á(S)	á(S)	225
â	â	-	-	226
∣	∣	-	-	227
ä	ä	ä	ä (D)	228
â	â	-	-	229
æ	æ	-	æ	230
ç	ç	ç (F)	ç (F)	231
è	è	è (F/I)	è (F/I)	232
é	é	é (F/S)	é (F/S)	233
ê	ê	-	-	234
ë	ë	-	-	235
ì	ì	ì (I)	ì (I)	236
í	í	í(S)	í(S)	237
î	î	-	-	238
ï	ï	-	-	239
∫	∫	-	-	240
ñ	ñ	-	-	241
ò	ò	ò (I)	ò (I)	242
ó	ó	ó (F/S)	ó (F/S)	243
ô	ô	-	-	244
≈	≈	-	-	245
ö	ö	ö	ö (D)	246
÷	÷	÷	-	247
√	√	√	-	248
ù	ù	ù (F/I)	ù (F/I)	249
ú	ú	ú(S)	ú(S)	250
û	û	-	-	251
ü	ü	ü	ü (D)	252
ⁿ	ⁿ	-	-	253
■	■	-	-	254
ÿ	ÿ	-	-	255