

## Measured Components of PN-Rea V9.0 (ID31)

Component		Type	MLFB	Version
IO controller	S7-1200	CPU 1212C	6ES7212-1AE40-0XB0	V 4.1
		CPU 1217C	6ES7217-1AG40-0XB0	V 4.1
	S7-1500	CPU 1513-1PN	6ES7513-1AL00-0AB0	V 1.5
		CPU 1516-2PN/DP	6ES7516-3AN00-0AB0	V 1.5
		CPU 1518-	6ES7518-4AP00-0AB0	V 1.5
		CPU 1512SP-1PN	6ES7512-1DK00-0AB0	V 1.0
	SW Controller	CPU 1507S	6ES7672-7AC00-0YA0	V 1.8
		IPC 427D + IE	6AG4140-5BK04-0EB0	Core i3, 1,6 GHz, PN-IRT, 2GB + NVRAM; Win7 embedded; CFAST 16GB
		IPCI PC 627D + IE	6AG4131-2CM20-0AX0	Celeron 2,2 GHz PN CP1616, 2MB SRAM, SSD 240GB, 4GB RAM, Win7 Ultimate
		CPU-1515SP PC	6ES7677-2AA41-0FB0	V 1.8
PROFINET Driver	IPC 427D + IE	6ES7195-3AA00-0YA0	V1.0	
IO devices	ET200SP	IM PN interface module Standard	6ES7155-6AA00-0BN0	V 1.1
		IM PN interface module high feature	6ES7155-6AU00-0CN0	V 2.2
		I/O module (8 DO HF)	6ES7 132-6BF00-0CA0	
		I/O module (8 DI HF)	6ES7 131-6BF00-0CA0	
		I/O Module (16 DI	6ES7 131-6BH00-0BA0	
		I/O module (16 DO)	6ES7 132-6BH00-0BA0	
		I/O module (2 AQ)	6ES7 532-5HF00-0AB0	
		I/O module (2 AI)	6ES7 134-6HB00-0DA1	
		CM IO-Link	6ES7137-6BD00-0BA0	
	ET200MP	IM155-5 PN ST	6ES7155-5AA00-0AB0	V 2.0
		IM155-5 PN HF	6ES7155-5AA00-0AC0	V 1.0
		I/O module (16 DI HF)	6ES7 521-1BH00-0AB0	
		I/O module (16 DO)	6ES7 522-1BH00-0AB0	
		I/O module (32 DI HF)	6ES7 521-1BL00-0AB0	
		I/O module (32 DO)	6ES7 522-1BL00-0AB0	

Component		Type	MLFB	Version
		I/O module (8 AI)	6ES7 531-7NF10-0AB0	
		I/O module (8 AQ)	6ES7 532-5HF00-0AB0	
S7-1200 Peripherie	Signalboard	DI/DO	6ES7 223-0BD30-0XB0	
		16 DI/DO	6ES7 223-1BL30-0XB0	
		8 DI/DO	6ES7 223-1BH32-0XB0	
		4AI/2AQ	6ES7 234-4HE32-0XB0	