

**Umschlüsselungsliste für elektronische Überlastrelais 3RB10 auf 3RB20 / 3RB21**

**Conversion list for electronic overload relays 3RB10 to 3RB20 / 3RB21**

					Stand / dated: 03/2006
alt	Einstellbereich	CLASS	neu	Einstellbereich	CLASS
old	setting range	CLASS	new	setting range	CLASS
3RB1016-1RB0	(0,1 ... 0,4 A)	10	3RB2016-1RB0	(0,1 ... 0,4 A)	10
3RB1016-1NB0	(0,4 ... 1,6 A)	10	3RB2016-1NB0	(0,32 ... 1,25 A)	10
		10	3RB2016-1PB0	(1 ... 4 A)	10
3RB1016-1PB0	(1,5 ... 6 A)	10	3RB2016-1PB0	(1 ... 4 A)	10
		10	3RB2016-1SB0	(3 ... 12 A)	10
3RB1016-1SB0	(3 ... 12 A)	10	3RB2016-1SB0	(3 ... 12 A)	10
3RB1026-1RB0	(0,1 ... 0,4 A)	10	3RB2016-1RB0	(0,1 ... 0,4 A)	10
3RB1026-1NB0	(0,4 ... 1,6 A)	10	3RB2016-1NB0	(0,32 ... 1,25 A)	10
		10	3RB2016-1PB0	(1 ... 4 A)	10
3RB1026-1PB0	(1,5 ... 6 A)	10	3RB2016-1PB0	(1 ... 4 A)	10
		10	3RB2016-1SB0	(3 ... 12 A)	10
3RB1026-1SB0	(3 ... 12 A)	10	3RB2026-1SB0	(3 ... 12 A)	10
3RB1026-1QB0	(6 ... 25 A)	10	3RB2026-1QB0	(6 ... 25 A)	10
3RB1036-1QB0	(6 ... 25 A)	10	3RB2036-1QB0	(6 ... 25 A)	10
3RB1036-1UB0	(13 ... 50 A)	10	3RB2036-1UB0	(12,5 ... 50 A)	10
3RB1046-1UB0	(13 ... 50 A)	10	3RB2046-1UB0	(12,5 ... 50 A)	10
3RB1046-1EB0	(25 ... 100 A)	10	3RB2046-1EB0	(25 ... 100 A)	10
3RB1056-1FW0	(50 ... 200 A)	10	3RB2056-1FW2	(50 ... 200 A)	10
3RB1056-1FG0	(50 ... 200 A)	10	3RB2056-1FC2	(50 ... 200 A)	10
3RB1066-1GG0	(55 ... 250 A)	10	3RB2066-1GC2	(55 ... 250 A)	10
3RB1066-1KG0	(200 ... 540 A)	10	3RB2066-1MC2	(160 ... 630 A)	10
3RB1066-1LGO	(300 ... 630 A)	10	3RB2066-1MC2	(160 ... 630 A)	10
3RB1016-2RB0	(0,1 ... 0,4 A)	20	3RB2016-2RB0	(0,1 ... 0,4 A)	20
3RB1016-2NB0	(0,4 ... 1,6 A)	20	3RB2016-2NB0	(0,32 ... 1,25 A)	20
		20	3RB2016-2PB0	(1 ... 4 A)	20
3RB1016-2PB0	(1,5 ... 6,0 A)	20	3RB2016-2PB0	(1 ... 4 A)	20
		20	3RB2016-2SB0	(3 ... 12 A)	20
3RB1016-2SB0	(3,0 ... 12,0 A)	20	3RB2016-2SB0	(3 ... 12 A)	20
3RB1026-2RB0	(0,1 ... 0,4 A)	20	3RB2016-2RB0	(0,1 ... 0,4 A)	20
3RB1026-2NB0	(0,4 ... 1,6 A)	20	3RB2016-2NB0	(0,32 ... 1,25 A)	20
		20	3RB2016-2PB0	(1 ... 4 A)	20
3RB1026-2PB0	(1,5 ... 6 A)	20	3RB2016-2PB0	(1 ... 4 A)	20
		20	3RB2016-2SB0	(3 ... 12 A)	20
3RB1026-2SB0	(3 ... 12 A)	20	3RB2026-2SB0	(3 ... 12 A)	20
3RB1026-2QB0	(6 ... 25 A)	20	3RB2026-2QB0	(6 ... 25 A)	20
3RB1036-2QB0	(6 ... 25 A)	20	3RB2036-2QB0	(6 ... 25 A)	20
3RB1036-2UB0	(13 ... 50 A)	20	3RB2036-2UB0	(12,5 ... 50 A)	20
3RB1046-2UB0	(13 ... 50 A)	20	3RB2046-2UB0	(12,5 ... 50 A)	20
3RB1046-2EB0	(25 ... 100 A)	20	3RB2046-2EB0	(25 ... 100 A)	20
3RB1056-2FW0	(50 ... 200 A)	20	3RB2056-2FW2	(50 ... 200 A)	20
3RB1056-2FG0	(50 ... 200 A)	20	3RB2056-2FC2	(50 ... 200 A)	20
3RB1066-2GG0	(55 ... 250 A)	20	3RB2066-2GC2	(55 ... 250 A)	20
3RB1066-2KG0	(200 ... 540 A)	20	3RB2066-2MC2	(160 ... 630 A)	20
3RB1066-2LGO	(300 ... 630 A)	20	3RB2066-2MC2	(160 ... 630 A)	20
3RB1016-1RB0	(0,1 ... 0,4 A)	10	3RB2113-4RB0	(0,1 ... 0,4 A)	5, 10, 20, 30 einstellbar / selectable
3RB1016-1NB0	(0,4 ... 1,6 A)	10	3RB2113-4NB0	(0,32 ... 1,25 A)	5, 10, 20, 30 einstellbar / selectable
		10	3RB2113-4PB0	(1 ... 4 A)	5, 10, 20, 30 einstellbar / selectable
3RB1016-1PB0	(1,5 ... 6,0 A)	10	3RB2113-4PB0	(1 ... 4 A)	5, 10, 20, 30 einstellbar / selectable
		10	3RB2113-4SB0	(3 ... 12 A)	5, 10, 20, 30 einstellbar / selectable
3RB1016-1SB0	(3,0 ... 12,0 A)	10	3RB2113-4SB0	(3 ... 12 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-1RB0	(0,1 ... 0,4 A)	10	3RB2113-4RB0	(0,1 ... 0,4 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-1NB0	(0,4 ... 1,6 A)	10	3RB2113-4NB0	(0,32 ... 1,25 A)	5, 10, 20, 30 einstellbar / selectable
		10	3RB2113-4PB0	(1 ... 4 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-1PB0	(1,5 ... 6 A)	10	3RB2113-4PB0	(1 ... 4 A)	5, 10, 20, 30 einstellbar / selectable
		10	3RB2113-4SB0	(3 ... 12 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-1SB0	(3 ... 12 A)	10	3RB2123-4SB0	(3 ... 12 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-1QB0	(6 ... 25 A)	10	3RB2123-4QB0	(6 ... 25 A)	5, 10, 20, 30 einstellbar / selectable
3RB1036-1QB0	(6 ... 25 A)	10	3RB2133-4QB0	(6 ... 25 A)	5, 10, 20, 30 einstellbar / selectable
3RB1036-1UB0	(13 ... 50 A)	10	3RB2133-4UB0	(12,5 ... 50 A)	5, 10, 20, 30 einstellbar / selectable
3RB1046-1UB0	(13 ... 50 A)	10	3RB2143-4UB0	(12,5 ... 50 A)	5, 10, 20, 30 einstellbar / selectable
3RB1046-1EB0	(25 ... 100 A)	10	3RB2143-4EB0	(25 ... 100 A)	5, 10, 20, 30 einstellbar / selectable
3RB1056-1FW0	(50 ... 200 A)	10	3RB2153-4FW2	(50 ... 200 A)	5, 10, 20, 30 einstellbar / selectable
3RB1056-1FG0	(50 ... 200 A)	10	3RB2153-4FC2	(50 ... 200 A)	5, 10, 20, 30 einstellbar / selectable
3RB1066-1GG0	(55 ... 250 A)	10	3RB2163-4GC2	(55 ... 250 A)	5, 10, 20, 30 einstellbar / selectable
3RB1066-1KG0	(200 ... 540 A)	10	3RB2163-4MC2	(160 ... 630 A)	5, 10, 20, 30 einstellbar / selectable
3RB1066-1LGO	(300 ... 630 A)	10	3RB2163-4MC2	(160 ... 630 A)	5, 10, 20, 30 einstellbar / selectable
3RB1016-2RB0	(0,1 ... 0,4 A)	20	3RB2113-4RB0	(0,1 ... 0,4 A)	5, 10, 20, 30 einstellbar / selectable
3RB1016-2NB0	(0,4 ... 1,6 A)	20	3RB2113-4NB0	(0,32 ... 1,25 A)	5, 10, 20, 30 einstellbar / selectable
		20	3RB2113-4PB0	(1 ... 4 A)	5, 10, 20, 30 einstellbar / selectable
3RB1016-2PB0	(1,5 ... 6,0 A)	20	3RB2113-4PB0	(1 ... 4 A)	5, 10, 20, 30 einstellbar / selectable
		20	3RB2113-4SB0	(3 ... 12 A)	5, 10, 20, 30 einstellbar / selectable
3RB1016-2SB0	(3,0 ... 12,0 A)	20	3RB2113-4SB0	(3 ... 12 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-2RB0	(0,1 ... 0,4 A)	20	3RB2113-4RB0	(0,1 ... 0,4 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-2NB0	(0,4 ... 1,6 A)	20	3RB2113-4NB0	(0,32 ... 1,25 A)	5, 10, 20, 30 einstellbar / selectable
		20	3RB2113-4PB0	(1 ... 4 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-2PB0	(1,5 ... 6 A)	20	3RB2113-4PB0	(1 ... 4 A)	5, 10, 20, 30 einstellbar / selectable
		20	3RB2113-4SB0	(3 ... 12 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-2SB0	(3 ... 12 A)	20	3RB2123-4SB0	(3 ... 12 A)	5, 10, 20, 30 einstellbar / selectable
3RB1026-2QB0	(6 ... 25 A)	20	3RB2123-4QB0	(6 ... 25 A)	5, 10, 20, 30 einstellbar / selectable
3RB1036-2QB0	(6 ... 25 A)	20	3RB2133-4QB0	(6 ... 25 A)	5, 10, 20, 30 einstellbar / selectable
3RB1036-2UB0	(13 ... 50 A)	20	3RB2133-4UB0	(12,5 ... 50 A)	5, 10, 20, 30 einstellbar / selectable
3RB1046-2UB0	(13 ... 50 A)	20	3RB2143-4UB0	(12,5 ... 50 A)	5, 10, 20, 30 einstellbar / selectable
3RB1046-2EB0	(25 ... 100 A)	20	3RB2143-4EB0	(25 ... 100 A)	5, 10, 20, 30 einstellbar / selectable
3RB1056-2FW0	(50 ... 200 A)	20	3RB2153-4FW2	(50 ... 200 A)	5, 10, 20, 30 einstellbar / selectable
3RB1056-2FG0	(50 ... 200 A)	20	3RB2153-4FC2	(50 ... 200 A)	5, 10, 20, 30 einstellbar / selectable
3RB1066-2GG0	(55 ... 250 A)	20	3RB2163-4GC2	(55 ... 250 A)	5, 10, 20, 30 einstellbar / selectable
3RB1066-2KG0	(200 ... 540 A)	20	3RB2163-4MC2	(160 ... 630 A)	5, 10, 20, 30 einstellbar / selectable
3RB1066-2LGO	(300 ... 630 A)	20	3RB2163-4MC2	(160 ... 630 A)	5, 10, 20, 30 einstellbar / selectable