

| Module | Article number | Firmware |
|---|--------------------|--------------------------|
| SIMATIC NET PC-Software / PN driver unit | | |
| CP 1616 | 6GK1161-6AA02 | from V2.0 |
| | 6GK1161-6AA01 | |
| | 6GK1161-6AA00 | |
| CP 1604 | 6GK1160-4AA01 | from V2.0 |
| | 6GK1160-4AA00 | |
| SOFTNET PROFINET IO | 6GK1704-1HW71-3AA0 | from V7.1 (Edition 2008) |
| Embedded and PC-based Automation | | |
| WinAC RTX 2008 | 6ES7671-0RC06-0YA0 | V4.4 |
| WinAC RTX (F) 2009 | 6ES7671-0RC07-0YA0 | V4.5 |
| | 6ES7671-1RC07-0YA0 | |
| WinAC RTX (F) 2010 | 6ES7671-0RC08-0YA0 | V4.6 |
| | 6ES7671-1RC08-0YA0 | |
| S7-mEC, EC31-RTX | 6ES7677-1DD00-0BB0 | from V4.4 |
| | 6ES7677-1DD10-0BB0 | |
| S7-400 CPUs | | |
| CPU 410-5H | 6ES7410-5HX08-0AB0 | from V8.0 |
| CPU 412-2 PN | 6ES7412-2EK06-0AB0 | from V6.0 |
| | 6ES7412-2EK07-0AB0 | from V7.0 |
| CPU 414-3 PN/DP | 6ES7414-3EM05-0AB0 | from V5.0 |
| | 6ES7414-3EM06-0AB0 | from V6.0 |
| | 6ES7414-3EM07-0AB0 | from V7.0 |
| CPU 414F-3 PN/DP | 6ES7414-3FM06-0AB0 | from V6.0 |
| | 6ES7414-3FM07-0AB0 | from V7.0 |
| CPU 416-3 PN/DP | 6ES7416-3ER05-0AB0 | from V5.0 |
| | 6ES7416-3ES06-0AB0 | from V6.0 |
| | 6ES7416-3ES07-0AB0 | from V7.0 |
| CPU 416F-3 PN/DP | 6ES7416-3FR05-0AB0 | from V5.0 |
| | 6ES7416-3FS06-0AB0 | from V6.0 |
| | 6ES7416-3FS07-0AB0 | from V7.0 |
| CPU 412-5H PN/DP | 6ES7412-5HK06-0AB0 | from V6.0 |
| CPU 414-5H PN/DP | 6ES7414-5HM06-0AB0 | from V6.0 |
| CPU 416-5H PN/DP | 6ES7416-5HS06-0AB0 | from V6.0 |
| CPU 417-5H PN/DP | 6ES7416-5HT06-0AB0 | from V6.0 |
| S7-300 CPUs | | |
| CPU 314C-2 PN/DP | 6ES7314-6EH04-0AB0 | from V3.3 |
| CPU 315-2 PN/DP | 6ES7315-2EH13-0AB0 | from V2.5 |
| | 6ES7315-2EH14-0AB0 | from V3.1 |
| CPU 315F-2 PN/DP | 6ES7315-2FH13-0AB0 | from V2.5 |
| | 6ES7315-2FJ14-0AB0 | from V3.1 |
| CPU 315T-3 PN/DP | 6ES7315-7TJ10-0AB0 | from V3.2 |
| CPU 317-2 PN/DP | 6ES7317-2EK13-0AB0 | from V2.5 |
| | 6ES7317-2EK14-0AB0 | from V3.1 |
| CPU 317F-2 PN/DP | 6ES7317-2FK13-0AB0 | from V2.5 |
| | 6ES7317-2FK14-0AB0 | from V3.1 |
| CPU 317T-3 PN/DP | 6ES7317-7TK10-0AB0 | from V3.2 |
| CPU 317TF-3 PN/DP | 6ES7317-7UL10-0AB0 | from V3.2 |
| CPU 319-3 PN/DP | 6ES7318-3EL00-0AB0 | from V2.5 |
| | 6ES7318-3EL01-0AB0 | from V3.2 |
| CPU 319F-3 PN/DP | 6ES7318-3FL00-0AB0 | from V2.5 |
| | 6ES7318-3FL01-0AB0 | from V3.2 |
| ET 200S CPUs | | |
| IM 151-8 PN/DP CPU | 6ES7151-8AB00-0AB0 | from V2.7 |
| | 6ES7151-8AB01-0AB0 | from V3.2 |
| IM 151-8F PN/DP CPU | 6ES7151-8FB00-0AB0 | from V2.7 |
| | 6ES7151-8FB01-0AB0 | from V3.2 |

| Module | Article number | Firmware |
|-----------------------|--------------------|-----------|
| ET 200pro CPUs | | |
| IM 154-8 CPU | 6ES7154-8AB00-0AB0 | from V2.5 |
| | 6ES7154-8AB01-0AB0 | from V3.2 |
| IM 154-8F CPU | 6ES7154-8FB01-0AB0 | from V3.2 |
| IM 154-8FX CPU | 6ES7154-8FX00-0AB0 | from V3.2 |
| CPU 1513pro-2 PN | 6ES7513-2PL00-0AB0 | from V2.8 |
| CPU 1513pro F-2 PN | 6ES7513-2GL00-0AB0 | from V2.8 |
| CPU 1516pro-2 PN | 6ES7516-2PN00-0AB0 | from V2.0 |
| CPU 1516pro F-2 PN | 6ES7516-2GN00-0AB0 | from V2.0 |
| S7-1500 CPUs | | |
| CPU 1518-4 PN/DP | 6ES7518-4AP00-0AB0 | from V1.5 |
| CPU 1518-4 PN/DP ODK | 6ES7518-4AP00-3AB0 | from V2.0 |
| CPU 1518-4 PN/DP MFP | 6ES7518-4AX00-1AC0 | from V2.5 |
| CPU 1518F-4 PN/DP | 6ES7518-4FP00-0AB0 | from V1.5 |
| CPU 1518F-4 PN/DP ODK | 6ES7518-4FP00-3AB0 | from V2.0 |
| CPU 1518F-4 PN/DP MFP | 6ES7518-4FX00-1AC0 | from V2.5 |
| CPU 1517-3 PN/DP | 6ES7517-3AP00-0AB0 | from V1.6 |
| CPU 1517F-3 PN/DP | 6ES7517-3FP00-0AB0 | from V1.6 |
| CPU 1516-3 PN/DP | 6ES7516-3AN00-0AB0 | from V1.0 |
| | 6ES7516-3AN01-0AB0 | from V1.8 |
| CPU 1516F-3 PN/DP | 6ES7516-3FN00-0AB0 | from V1.5 |
| | 6ES7516-3FN01-0AB0 | from V1.8 |
| CPU 1515-2 PN | 6ES7515-2AM00-0AB0 | from V1.5 |
| | 6ES7515-2AM01-0AB0 | from V1.8 |
| CPU 1515F-2 PN | 6ES7515-2FM00-0AB0 | from V1.6 |
| | 6ES7515-2FM01-0AB0 | from V1.8 |
| CPU 1513-1 PN | 6ES7513-1AL00-0AB0 | from V1.0 |
| | 6ES7513-1AL01-0AB0 | from V1.8 |
| CPU 1513F-1 PN | 6ES7513-1FL00-0AB0 | from V1.7 |
| | 6ES7513-1FL01-0AB0 | from V1.8 |
| CPU 1511-1 PN | 6ES7511-1AK00-0AB0 | from V1.0 |
| | 6ES7511-1AK01-0AB0 | from V1.8 |
| | 6ES7511-1AK02-0AB0 | from V2.5 |
| CPU 1511F-1 PN | 6ES7511-1FK00-0AB0 | from V1.7 |
| | 6ES7511-1FK01-0AB0 | from V1.8 |
| | 6ES7511-1FK02-0AB0 | from V2.5 |
| CPU 1511C-1 PN | 6ES7511-1CK00-0AB0 | from V1.8 |
| | 6ES7511-1CK01-0AB0 | from V2.5 |
| CPU 1512C-1 PN | 6ES7512-1CK00-0AB0 | from V1.8 |
| | 6ES7512-1CK01-0AB0 | from V2.5 |
| CPU 1511T-1 PN | 6ES7511-1TK01-0AB0 | from V2.0 |
| CPU 1511TF-1 PN | 6ES7511-1UK01-0AB0 | from V2.1 |
| CPU 1515T-2 PN | 6ES7515-2TM01-0AB0 | from V2.0 |
| CPU 1515TF-2 PN | 6ES7515-2UM01-0AB0 | from V2.1 |
| CPU 1516-3T PN/DP | 6ES7516-3TN00-0AB0 | from V2.5 |
| CPU 1516-3TF PN/DP | 6ES7516-3UN00-0AB0 | from V2.5 |
| CPU 1517T-3 PN/DP | 6ES7517-3TP00-0AB0 | from V2.0 |
| CPU 1517TF-3 PN/DP | 6ES7517-3UP00-0AB0 | from V2.0 |
| CPU 1513R-1 PN | 6ES7513-1RL00-0AB0 | from V2.6 |
| CPU 1515R-2 PN | 6ES7515-2RM00-0AB0 | from V2.6 |
| CPU 1517H-3 PN | 6ES7517-3HP00-0AB0 | from V2.6 |

This entry is from the Service&Support portal of Siemens AG,
Siemens Industry Online Support.

The general terms of use

| Module | Article number | Firmware |
|------------------------------------|--------------------|-----------|
| ET 200SP CPUs | | |
| CPU 1510SP-1 PN | 6ES7510-1DJ00-0AB0 | from V1.6 |
| | 6ES7510-1DJ01-0AB0 | from V1.8 |
| CPU 1510SP F-1 PN | 6ES7510-1SJ00-0AB0 | from V1.7 |
| | 6ES7510-1SJ01-0AB0 | from V1.8 |
| CPU 1512SP-1 PN | 6ES7512-1DK00-0AB0 | from V1.6 |
| | 6ES7512-1DK01-0AB0 | from V1.8 |
| CPU 1512SP F-1 PN | 6ES7512-1SK00-0AB0 | from V1.7 |
| | 6ES7512-1SK01-0AB0 | from V1.8 |
| CPU 1515SP PC 2 | 6ES7677-2DB40-0GB0 | from V2.5 |
| | 6ES7677-2DB42-0GB0 | |
| | 6ES7677-2DB42-0GK0 | |
| | 6ES7677-2DB42-0GL0 | |
| | 6ES7677-2DB42-0GM0 | |
| CPU 1515SP PC 2 F | 6ES7677-2SB40-0GB0 | from V2.5 |
| | 6ES7677-2SB42-0GB0 | |
| | 6ES7677-2SB42-0GK0 | |
| | 6ES7677-2SB42-0GL0 | |
| | 6ES7677-2SB42-0GM0 | |
| CPU 1515SP PC2 T | 6ES7677-2VB42-0GB0 | from V2.5 |
| CPU 1515SP PC2 TF | 6ES7677-2WB42-0GB0 | from V2.5 |
| CPU 1515SP PC | 6ES7677-2AA31-0EB0 | from V1.7 |
| | 6ES7677-2AA41-0FB0 | |
| | 6ES7677-2AA41-0FK0 | |
| | 6ES7677-2AA41-0FL0 | |
| | 6ES7677-2AA41-0FM0 | |
| CPU 1515SP PC F | 6ES7677-2FA31-0EB0 | from V2.0 |
| | 6ES7677-2FA41-0FB0 | |
| | 6ES7677-2FA41-0FK0 | |
| | 6ES7677-2FA41-0FL0 | |
| | 6ES7677-2FA41-0FM0 | |
| S7-1500 Software Controller | | |
| CPU 1507S | 6ES7672-7AC00-0YA0 | from V1.8 |
| | 6ES7672-7AC00-0YG0 | from V2.0 |
| | 6ES7672-7AC01-0YA0 | |
| | 6ES7672-7AC01-0YG0 | |
| | 6ES7672-7AC01-0YK0 | |
| CPU 1508S | 6ES7672-8AC01-0YA0 | from V2.6 |
| | 6ES7672-8AC01-0YG0 | |
| CPU 1507S F | 6ES7672-7FC01-0YA0 | from V2.0 |
| | 6ES7672-7FC01-0YG0 | |
| CPU 1508S F | 6ES7672-8FC01-0YA0 | from V2.6 |
| | 6ES7672-8FC01-0YG0 | |

| Module | Article number | Firmware |
|--|--------------------|-----------|
| S7-1200 CPUs | | |
| CPU 1211C | 6ES7211-1AD30-0XB0 | from V1.0 |
| | 6ES7211-1BD30-0XB0 | |
| | 6ES7211-1HD30-0XB0 | |
| | 6ES7211-1AE31-0XB0 | from V3.0 |
| | 6ES7211-1BE31-0XB0 | |
| | 6ES7211-1HE31-0XB0 | |
| | 6ES7211-1AE40-0XB0 | from V4.0 |
| | 6ES7211-1BE40-0XB0 | |
| 6ES7211-1HE40-0XB0 | | |
| CPU 1212C | 6ES7212-1AD30-0XB0 | from V1.0 |
| | 6ES7212-1BD30-0XB0 | |
| | 6ES7212-1HD30-0XB0 | |
| | 6ES7212-1AE31-0XB0 | from V3.0 |
| | 6ES7212-1BE31-0XB0 | |
| | 6ES7212-1HE31-0XB0 | |
| | 6ES7212-1AE40-0XB0 | from V4.0 |
| | 6ES7212-1BE40-0XB0 | |
| 6ES7212-1HE40-0XB0 | | |
| CPU 1212 FC | 6ES7212-1AF40-0XB0 | from V4.2 |
| | 6ES7212-1HF40-0XB0 | |
| CPU 1214C | 6ES7214-1AE30-0XB0 | from V1.0 |
| | 6ES7214-1BE30-0XB0 | |
| | 6ES7214-1HE30-0XB0 | |
| | 6ES7214-1AG31-0XB0 | from V3.0 |
| | 6ES7214-1BG31-0XB0 | |
| | 6ES7214-1HG31-0XB0 | |
| | 6ES7214-1AG40-0XB0 | from V4.0 |
| | 6ES7214-1BG40-0XB0 | |
| 6ES7214-1HG40-0XB0 | | |
| CPU 1214 FC | 6ES7214-1AF40-0XB0 | from V4.0 |
| | 6ES7214-1HF40-0XB0 | |
| CPU 1215C | 6ES7215-1AG31-0XB0 | from V3.0 |
| | 6ES7215-1BG31-0XB0 | |
| | 6ES7215-1HG31-0XB0 | |
| | 6ES7215-1AG40-0XB0 | from V4.0 |
| | 6ES7215-1BG40-0XB0 | |
| 6ES7215-1HG40-0XB0 | | |
| CPU 1215 FC | 6ES7215-1AF40-0XB0 | from V4.0 |
| | 6ES7215-1HF40-0XB0 | |
| CPU 1217C | 6ES7217-1AG40-0XB0 | from V4.0 |
| Industrial Ethernet CPs S7-300/S7-400 | | |
| CP 343-1 Standard | 6GK7343-1EX30-0XE0 | from V2.2 |
| CP 343-1 Advanced | 6GK7343-1GX30-0XE0 | from V1.0 |
| | 6GK7343-1GX31-0XE0 | from V3.0 |
| CP 443-1 Standard | 6GK7443-1EX20-0XE0 | from V1.0 |
| | 6GK7443-1EX30-0XE0 | from V3.0 |
| CP 443-1 Advanced | 6GK7443-1GX20-0XE0 | from V2.0 |
| | 6GK7443-1GX30-0XE0 | from V3.0 |
| Industrial Ethernet CMs | | |
| CM 1242-1 | 6GK7542-1AX00-0XE0 | from V1.0 |