



Distance for FS315 **X** [mm]

|        |
|--------|
| S = 35 |
| M = 35 |
| L = 70 |

| Frame Size                  | 1LG4/6 Motore | 18.   | 20.   | 22.-2 | 22.-4 ... -8 | 25.-2 | 25.-4 ... -8 | 28.-2 | 28.-4 ... -8 | 31.-2                   | 31.-4 ... -8 |
|-----------------------------|---------------|-------|-------|-------|--------------|-------|--------------|-------|--------------|-------------------------|--------------|
| Distance                    | <b>X</b> [mm] | 26    | 25    | 25    | 25           | 30    | 30           | 30    | 30           | depending on frame size |              |
| Mounting hole dimensions    | [mm]          | 15*19 | 19*25 | 19*25 | 24*30        | 24*30 | 24*30        | 24*30 | 24*30        | 28*35                   | 28*35        |
| Mounting height of the foot | <b>Y</b> [mm] | 20    | 34    | 34    | 40           | 40    | 40           | 40    | 40           | 50                      | 50           |