

3RV1 MCCB额定电流运行时 (In) 的功率损耗

三相主回路的总和

订货编号	额定电流 In	功率损耗 (瓦)
3RV1063-7AL10	100 A	5.10
3RV1063-7CL10	160 A	13.20
3RV1063-7DL10	200 A	20.70
3RV1073-7GL10	400 A	49.50
3RV1083-7JL10	630 A	90.00
3RV1353-6AP10	1,0 A	4.50
3RV1353-6BP10	1,6 A	6.30
3RV1353-6CP10	2,0 A	7.50
3RV1353-6DP10	3,2 A	8.70
3RV1353-6EP10	4,0 A	7.80
3RV1353-6FP10	5,0 A	8.70
3RV1353-6GP10	6,5 A	10.50
3RV1353-6HP10	8,5 A	9.00
3RV1353-6JP10	12,5 A	3.30
3RV1353-6LM10	20 A	5.10
3RV1353-6MM10	32 A	8.10
3RV1363-7AN10	100 A	5.10
3RV1363-7CN10	160 A	13.20
3RV1363-7EN10	250 A	32.10
3RV1373-7GN10	400 A	49.50
3RV1373-7JN10	630 A	123.00
3RV1383-7JN10	630 A	90.00
3RV1383-7KN10	800 A	96.00
3RV1364-7AN10	100 A	5.10
3RV1364-7CN10	160 A	13.20
3RV1364-7EN10	250 A	32.10
3RV1374-7GN10	400 A	49.50