



Table 2		Distance between circuit-breaker and earthed metal parts			
Type		Distance			
Limiter	Circuit breaker	Ue	X	Y	Z
		V	mm	mm	mm
3RV2321-4EC10	3RV2.1./3RV2.2.	500	90	40	10
		690	90	60	30
3RV1331-4HC10	3RV2.1./3RV2.2.	690	140	60	10



front view



side view

3RV2321-4EC10 + 3RV2.1./3RV2.2.

Test laboratory:

**Prüflaboratorium der Siemens AG  
I IA CE Amberg**

Authorized representative:


**Mr. Prechtl-Schöpf**

Date:


**2010-10-05**

Continuation  
Table 2

Distance between circuit-breaker and earthed metal parts



front view



side view

3RV1331-4HC10 + 3RV2.1./3RV2.2.

Test laboratory:

**Prüflaboratorium der Siemens AG**  
I IA CE Amberg

Authorized representative:

**Mr. Prechtl-Schöpf**

Date:

**2010-10-05**