

Digital Inputs

Type	Order Number
2DI DC24V	6ES7131-4BB01-0AA0
2DI DC24V	6ES7131-4BB01-0AB0
4DI DC24V	6ES7131-4BD01-0AA0
4DI DC24V	6ES7131-4BD01-0AB0
4DIImDC24V	6ES7131-4BD51-0AA0
8DI	6ES7131-4BF00-0AA0
4DI UC	6ES7131-4CD02-0AB0
2DI 120V	6ES7131-4EB00-0AB0
2DI 230V	6ES7131-4FB00-0AB0
4DI NAMUR	6ES7131-4RD00-0AB0

Digital Outputs

Type	Order Number
2DO DC24V	6ES7132-4BB01-0AA0
2DO DC24V	6ES7132-4BB01-0AB0
2DO DC24V	6ES7132-4BB31-0AA0
2DO DC24V	6ES7132-4BB31-0AB0
4DO HF 0,5A	6ES7132-4BD00-0AB0
4DO DC24V	6ES7132-4BD02-0AA0
4DO HF 2A	6ES7132-4BD30-0AB0
4DO DC24V	6ES7132-4BD32-0AA0
4DO DC24V	6ES7132-4BD50-0AA0
8DO	6ES7132-4BF00-0AA0
2DO 230V	6ES7132-4FB01-0AB0
2DO Rel.	6ES7132-4HB01-0AB0
2DO Rel.	6ES7132-4HB12-0AB0
2RO NO/NC	6ES7132-4HB50-0AB0

Analog Inputs

Type	Order Number
2AI U	6ES7134-4FB01-0AB0
2AI U HS	6ES7134-4FB52-0AB0
2AI I 2DMU	6ES7134-4GB01-0AB0
2AI I 4DMU	6ES7134-4GB11-0AB0
2AI I2DMU HS	6ES7134-4GB52-0AB0
2AI I4DMU HS	6ES7134-4GB62-0AB0
4AI I 2DMU	6ES7134-4GD00-0AB0
AI TC ST	6ES7134-4JB01-0AB0
2AI RTD ST	6ES7134-4JB51-0AB0
4AI RTD ST	6ES7134-4JB51-0AB0
4AI TC ST	6ES7134-4JD00-0AB0
2AI U	6ES7134-4LB02-0AB0
2AI I 2/4DMU	6ES7134-4MB02-0AB0
AI 2xTCHF	6ES7134-4NB01-0AB0
2AI RTDHF	6ES7134-4NB51-0AB0

Analog Outputs

Type	Order Number
-------------	---------------------

2AO U	6ES7135-4FB01-0AB0
2AO U HS	6ES7135-4FB52-0AB0
2AO I	6ES7135-4GB01-0AB0
2AO I HS	6ES7135-4GB52-0AB0
2AO U	6ES7135-4LB02-0AB0
2AO I	6ES7135-4MB02-0AB0

Power Modules

Type	Order Number
PM-E DC24V	6ES7138-4CA01-0AA0
PM24..48V	6ES7138-4CA50-0AB0
PM-E HF	6ES7138-4CA60-0AB0
PM-E AC230	6ES7138-4CB11-0AB0

Specialty / Technology Modules

Type	Order Number
4POTDIS	6ES7138-4FD00-0AA0
1CNT24V	6ES7138-4DA04-0AB0

Motor Starters

Type	Order Number
DS1e-x 3A	3RK1301-0AB10-0AA2
DS1e-x 3A	3RK1301-0AB10-0AA3
DS1e-x 3A	3RK1301-0AB10-0AA4
DS1e-x 3A	3RK1301-0AB10-0AB4
RS1e-x 3A	3RK1301-0AB10-1AA2
RS1e-x 3A	3RK1301-0AB10-1AA3
RS1e-x 3A	3RK1301-0AB10-1AA4
RS1e-x 3A	3RK1301-0AB10-1AB4
DSS1e-x 3A	3RK1301-0AB20-0AA2
DSS1e-x 3A	3RK1301-0AB20-0AA3
DSS1e-x 3A	3RK1301-0AB20-0AA4
DSS1e-x 3A	3RK1301-0AB20-0AB4
DS1e-x 8A	3RK1301-0BB10-0AA2
DS1e-x 8A	3RK1301-0BB10-0AA3
DS1e-x 8A	3RK1301-0BB10-0AA4
DS1e-x 8A	3RK1301-0BB10-0AB4
RS1e-x 8A	3RK1301-0BB10-1AA2
RS1e-x 8A	3RK1301-0BB10-1AA3
RS1e-x 8A	3RK1301-0BB10-1AA4
RS1e-x 8A	3RK1301-0BB10-1AB4
DSS1e-x 8A	3RK1301-0BB20-0AA2
DSS1e-x 8A	3RK1301-0BB20-0AA3
DSS1e-x 8A	3RK1301-0BB20-0AA4
DSS1e-x 8A	3RK1301-0BB20-0AB4
DS1e-x 16A	3RK1301-0CB10-0AA2
DS1e-x 16A	3RK1301-0CB10-0AA3
DS1e-x 16A	3RK1301-0CB10-0AA4
DS1e-x 16A	3RK1301-0CB10-0AB4
RS1e-x 16A	3RK1301-0CB10-1AA2

RS1e-x 16A	3RK1301-0CB10-1AA3
RS1e-x 16A	3RK1301-0CB10-1AA4
RS1e-x 16A	3RK1301-0CB10-1AB4
DSS1e-x 16A	3RK1301-0CB20-0AA2
DSS1e-x 16A	3RK1301-0CB20-0AA3
DSS1e-x 16A	3RK1301-0CB20-0AA4
DSS1e-x 16A	3RK1301-0CB20-0AB4
DS	3RK1301-xxB00-0AA0
DS-x	3RK1301-xxB00-0AA1
DS1-x	3RK1301-xxB00-0AA2
RS	3RK1301-xxB00-1AA0
RS-x	3RK1301-xxB00-1AA1
RS1-x	3RK1301-xxB00-1AA2
PM-D	3RK1903-0BA00
xB3 DC24V/4A	3RK1903-0CE00
xB4 DC500V/0.7A	3RK1903-0CF00
xB6 AC400V/0,5A	3RK1903-0CK00
F-CM	3RK1903-3CA00