

боковой поворотный привод для аварийного останова МЭК IP65 с монтажным кронштейном осветительный комплект 24 В DC принадлежность для: 3VA1 250



версия		
торговая марка изделия	SETRON	
принадлежности	Поворотный привод на боковой стенке	
Общие технические данные		
степень защиты IP	IP65	
Механическая конструкция		
высота	75 mm	
Сертификаты		
General Product Approval	EMV	Test Certificates



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

Marine / Shipping	other	Environment			
	Miscellaneous	Confirmation	Miscellaneous	Environmental Confirmations	Environmental Confirmations

Дополнительная информация
Информация об упаковке Информация об упаковке Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3VA9257-0PK57 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/ru/ps/3VA9257-0PK57 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9257-0PK57 CAx-Online-Generator http://www.siemens.com/cax Tender specifications http://www.siemens.com/specifications



