

SIMATIC IPC277G (nanopanel PC); 10" multi-touch (1280 x 800); 3x 10/100/1000 Mbps Ethernet RJ45; 2x display port graphic; 4x USB 3.1, 2x M.2 extension slot; 24 V DC industrial power supply Atom X6413E (4-core); 4 GB RAM; without COM; 256 GB Eco SSD; without hardware extension; Windows 10 IoT Enterprise 2019 LTSC, 64-bit, MUI (en/de/fr/it/es), ;

Display	
Design of display	10" TFT multi-touch
Screen diagonal	10 in
Resolution (pixels)	
• Horizontal image resolution	1 280 pixel
• Vertical image resolution	800 pixel
Backlighting	
• MTBF backlighting (at 25 °C)	50 000 h
Control elements	
Touch operation	
• Design as multi-touch screen	Yes; Projective-capacitive
Installation type/mounting	
central design	Yes
Mounting in portrait format possible	Yes
Power loss	
In full configuration	30 W
Dimensions	
Width of the housing front	280 mm
Height of housing front	205 mm
Mounting cutout, width	264 mm
Mounting cutout, height	189 mm
Overall depth	95 mm
Weights	
Weight, approx.	3.2 kg

Classifications			
		Version	Classification
	eClass	14	19-20-01-03
	eClass	12	19-20-01-03
	eClass	9.1	19-20-01-03
	eClass	9	19-20-01-03
	eClass	8	27-24-23-01
	eClass	7.1	27-24-23-01
	eClass	6	27-24-23-01
	ETIM	9	EC001414
	ETIM	8	EC001414
	ETIM	7	EC001414

Approvals / Certificates	
General Product Approval	



EG-Konf.



UL



RCM

[BIS CRS](#)

[KC](#)

For use in hazardous locations	Marine / Shipping
--------------------------------	-------------------



Marine / Shipping

[NK / Nippon Kaiji Kyokai](#)

[CCS \(China Classification Society\)](#)

last modified:

2/28/2023