

SINAMICS V20 200-240 V 1-phase-AC -10/+10 Rated power 2.2 kW with 150% overload for 60 sec. Integrated filter C2 I/O interface: 4 DI, 2 DQ, 2 AI, 1 AO Fieldbus: USS/Modbus RTU with built-in BOP Degree of protection IP20/UL open Size: Size C 184x182x169 (WxHxD)

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)

<https://support.industry.siemens.com/cs/products?mfn=ps&lc=en-WW>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>