

Berührungslose Sicherheitsschalter SIRIUS 3SE6 Magnet

Magnetschalter 3SE66, 3SE67

Kombination Überwachungseinheit – Magnetschalter

Überwachungseinheiten		Magnetschalter (Schaltelement + Schaltmagnet)			Erreichbarer SIL (IEC 61508, IEC 62061) Performance Level (EN ISO 13849-1)	
		1 S + 1 Ö 3SE6605-.BA.. 1 S + 1 Ö (+ 1 Ö Meldekontakt) 3SE6606-3BA	2 Ö 3SE6604-2BA.. 1 S + 2 Ö 3SE6606-2BA04	--		
						
		3SE6704-.BA	3SE6704-2BA			
		1 S + 1 Ö (+ 1 Ö Meldekontakt) 3SE6616-3CA01 3SE6626-3CA01	2 Ö; 2 Ö (+ 1 Ö Meldekontakt) 3SE6614-4CA01 3SE6624-4CA01 3SE6617-2CA01 3SE6627-2CA01 3SE6617-2CA04 3SE6617-2CA04 3SE6627-2CA04	2 Ö (+ 1 Ö Meldekontakt) 3SE6617-3CA01 3SE6627-3CA01 3SE6617-3CA04 3SE6627-3CA04		
						
		3SE6714-3CA 3SE6724-3CA	3SE6714-2CA 3SE6724-2CA	3SE6714-3CA 3SE6724-3CA		
Relaisausgang						
Sicherheitsschaltgeräte SIRIUS	3SK1111		--	✓	✓	SIL 3/PL e
	3SK1121, 3TK2826		✓	✓	✓	SIL 3/PL e
Elektronikausgang						
Sicherheitsschaltgeräte SIRIUS	3SK1112, 3SK1122		✓	✓	✓	SIL 3/PL e
	3SK2112, 3SK2122		✓	✓	✓	SIL 3/PL e
	3TK2845		--	✓	✓	SIL 3/PL e
Sichere Kompaktmodule ASIsafe	3RK1205, 3RK1405		--	✓	✓	SIL 3/PL e
Modulares Sicherheits- system (MSS)	3RK3		✓	✓	✓	SIL 3/PL e
SIMATIC S7-1200F oder SIMATIC S7-1500F	F-DI 16 x 24 V DC		✓	✓	✓	SIL 3/PL e
SIMATIC ET 200SP PROFIsafe	4/8 F-DI, DC 24 V		✓	✓	✓	SIL 3/PL e
SIMATIC ET 200eco	4/8 F-DI, DC 24 V		✓	✓	✓	SIL 3/PL e
SIMATIC ET 200pro	8/16 F-DI, DC 24 V, 4/8 F-DI / 4 F-DO 2 A, DC 24 V, F- Switch		✓	✓	✓	SIL 3/PL e

✓ geeigneter Magnetschalter

-- nicht vorhanden