


















Connection / Anschluss / Raccordement / Conexión / Connessione / Conexão / Ва'ланти / соединение / Połączenie / 连接		≤ 525V AC	690 V AC	
		3VA938.-0JB13 3VA938.-0JG13	—	D E F
		3VA948.-0JA13		
		3VA94...-0JJ23 3VA94...-0JC23 3VA93...-0JF60	D	
		3VA940.-0QA00	—	D E F
		3VA948.-0QB00	A B	D E F
		3VA948.-0QC00	B K	K L
		3VA948.-0QD00	D F	
		3VA948.-0QD00	B	
		3VA940.-0QA00	A B	
		3VA948.-0QB00	A B	
		3VA948.-0QC00	B K L	
		3VA948.-0QD00	D F	
		3VA948.-0QD00	B	



—: no barrier requirements / keine Isolationsanforderungen / Pas d'exigences de barrières / No hay requisitos de aislamiento entre fases / nessun requisito per barriera di separazione / não há requisitos de barreira / bariyer gereksinimleri yok / требования к барьеру отсутствуют / brak wymagań dot. barier / 无屏障要求














match barrier requirements / Isolationsanforderungen einhalten / Exigences de barrières respectées / Cumplir requisitos de aislamiento entre fases / coordinare i requisiti per barriera di separazione / corresponde aos requisitos da barreira / bariyer gereksinimlerini eşleştir / соответствуют требованиям к барьеру / dopasuj wymagania dot. barier / 匹配屏障要求

A			3VA9482-0WA00
B			3VA9482-0WA00
C			3VA9481-0WD.0
D			3VA9481-0WF.0
E			3VA9482-0WA00 3VA9481-0WJ.0
F			3VA9482-0WA00 3VA9481-0WJ.0
K		3VA9401-0WG.0	
L		3VA9482-0WA00 3VA9481-0WK.0	

Connection / Anschluss / Raccordement/ Conexión / Connessione / Conexão / Вађланти / соединение / Połączenie / 连接			≤ 525V AC	690 V AC
		3VA940.-0QE.0	C	M N
		3VA940.-0QF.0		
		3VA940.-0QA00	—	D E F
		3VA948.-0QB00	A B	D E F
		3VA948.-0QC00	K L	
		3VA948.-0QD00	D F	
		3VA948.-0QD00	B	
		3VA940.-0QA00	A B	D E F
		3VA948.-0QB00	A B	D F
		3VA948.-0QC00	K L	
		3VA948.-0QD00	F	
		3VA948.-0QD00	B	
		3VA940.-0QG00	O	

—: no barrier requirements / keine Isolationsanforderungen / Pas d'exigences de barrières / No hay requisitos de aislamiento entre fases / nessun requisito per barriera di separazione / não há requisitos de barreira / bariyer gereksinimleri yok / требования к барьеру отсутствуют / brak wymagań dot. barier / 无屏障要求

match barrier requirements / Isolationsanforderungen einhalten / Exigences de barrières respectées / Cumplir requisitos de aislamiento entre fases / coordinare i requisiti per barriera di separazione / corresponde aos requisitos da barreira / bariyer gereksinimlerini eşleştir / соответствуют требованиям к барьеру / dorasuj wymagania dot. barier / 匹配屏障要求

A			3VA9482-0WA00
B			3VA9482-0WA00
C			3VA9481-0WD.0
D			3VA9481-0WF.0
E			3VA9482-0WA00 3VA9481-0WJ.0
F			3VA9482-0WA00 3VA9481-0WJ.0
K			3VA9401-0WG.0
L			3VA9482-0WA00 3VA9481-0WK.0
M			3VA9482-0WA00 3VA9481-0WJ.0 3VA9481-0WD.0
N			3VA9482-0WA00 3VA9481-0WJ.0 3VA9481-0WD.0
O			3VA9482-0WA00