

LOGO! Device Series -- Compatibility Table

Product version	..0BA0			..0BA1			..0BA2			..0BA3	..0BA4	..0BA5	..0BA6		..0BA7	..0BA8	
	Basic	Long	Bus	Basic	Long	Bus	Basic	Long	Bus	Basic	Basic	Basic	Basic	3	Basic	1,2,3	4
LOGO!Soft V1.1	x	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
LOGO!Soft V2.x	x	x	x	-	-	-	-	-	-	-	-	-	-	-	-	-	-
LOGO!Soft V3.x	x	x	x	x	x	x	-	-	-	-	-	-	-	-	-	-	-
LOGO!Soft Comfort V1.0	x	x	x	x	x	x	-	-	-	-	-	-	-	-	-	-	-
LOGO!Soft Comfort V2.0	x	x	x	x	x	x	x	x	x	-	-	-	-	-	-	-	-
LOGO!Soft Comfort V3.x	x	x	x	x	x	x	x	x	x	x	-	-	-	-	-	-	-
LOGO!Soft Comfort V4.x	x	x	x	x	x	x	x	x	x	x	x	-	-	-	-	-	-
LOGO!Soft Comfort V5.x	x	x	x	x	x	x	x	x	x	x	x	x	-	-	-	-	-
LOGO!Soft Comfort V6.x	x	x	x	x	x	x	x	x	x	x	x	x	x	-	-	-	-
LOGO!Soft Comfort V6.1	x	x	x	x	x	x	x	x	x	x	x	x	x	x	-	-	-
LOGO!Soft Comfort V7.0	x	x	x	x	x	x	x	x	x	x	x	x	x	x	x	-	-
LOGO!Soft Comfort V8.0	x	x	x	x	x	x	x	x	x	x	x	x	x	x	x	x	-
LOGO!Soft Comfort V8.1	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x ¹⁾	x	x
Manual LOGO! 06/1996	x	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Manual LOGO! 1997	x	x	x	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Manual LOGO! 09/1999	x	x	x	x	x	x	-	-	-	-	-	-	-	-	-	-	-
Manual LOGO! 05/2000							x	x	x	-	-	-	-	-	-	-	-
Manual LOGO! 07/2001										x	-	-	-	-	-	-	-
Manual LOGO! 06/2003											x	-	-	-	-	-	-
Manual LOGO! 05/2006												x	-	-	-	-	-
Manual LOGO! 10/2008													x	-	-	-	-
Manual LOGO! 03/2009														x	-	-	-
Manual LOGO! 04/2011														x	x	x	-
Manual LOGO! 06/2014																	x
Manual LOGO! 07/2016																	x
Digital Inputs	6	12	12 + 4	6	12	12 + 4	6 (8)	12	12 + 4	8 (max.24)	8 (max. 24)	8 (max. 24)	8 (max. 24)	8 (max. 24)	8 (max. 24)	8 (max. 24)	
DI high speed (24V)	-	1 x 100Hz	1 x 100Hz	2 x 1kHz	2 x 1kHz	2 x 1kHz	2 x 1kHz	2 x 1kHz	2 x 1kHz	2 x 1kHz	2 x 2kHz	2 x 2kHz	4 x 5kHz	4 x 5kHz	4 x 5kHz		
Analog Inputs (24VDC)	-	-	-	-	-	-	2	-	-	2	2	2	4	4	4		
Digital Outputs	4	8	8 + 4	4	8	8 + 4	4	8	8 + 4	4 (max. 16)	4 (max. 16)	4 (max. 16)	4 (max. 16)	4 (max. 16)	4 (max. 16)	4 (max. 20)	
Flag Blocks	0	0	0	4	4	4	8	8	8	8	24	24	27	27	64		
max. number of blocks	30	30	30	56	56	56	56	56	56	56	130	130	200	400	400		
max. Times	10	10	10	16	16	16	16	16	16	16	130	130	200	400	400		
max. Counter	12	12	12	20	20	20	20	20	20	20	130	130	200	400	400		
max. Timer	4	4	4	8	8	8	8	8	8	8	130	130	200	400	400		
max. Message texts	0	0	0	0	0	0	5	5	5	5	10	10	50	50	50		

Date: 2016-12-30

1) The Version V8.1 of "LOGO! Soft Comfort" is suitable for all LOGO! hardware series (0BA0 to 0BA8). There cannot be downloaded programs that use the new special function blocks, reference parameters to the new special functions or special function block parameters to LOGO! devices prior to the 0BA8 series.