

Microsoft Windows Operation System	PROFIBUS PC CP													
	CP5623/24	CP5613/14 A3	CP5613/14 A2	CP5603	CP5613/14 CP5613/14 FO	CP5622	CP5621	CP5612	CP5611 A2	CP5611	CP5711	CP5512	CP5511	
Windows 10 (64 Bit) <sup>10)</sup>	X	X	X	X	-	X	X <sup>7)</sup>	X	X <sup>7)</sup>	-	X	-	-	
Windows 8.1 (64 Bit)	X	X	X	X	-	X	X <sup>7)</sup>	X	X <sup>7)</sup>	-	X	-	-	
Windows 8.1 (32 Bit)	X	X	X	X	-	X	X <sup>7)</sup>	X	X <sup>7)</sup>	-	X	-	-	
Windows 8 (64 Bit)	X	X <sup>6)</sup>	X	X	-	X	X <sup>7)</sup>	X	X <sup>7)</sup>	-	X	-	-	
Windows 8 (32 Bit)	X	X <sup>6)</sup>	X	X	-	X	X <sup>7)</sup>	X	X <sup>7)</sup>	-	X	-	-	
Windows 7 SP1 (64 Bit)	X	X <sup>6)</sup>	X	X	-	X <sup>5)</sup>	X <sup>4)7)</sup>	X <sup>5)</sup>	X <sup>4)7)</sup>	-	X	-	-	
Windows 7 SP1 (32 Bit)	X	X <sup>6)</sup>	X	X	-	X <sup>5)</sup>	X <sup>7)</sup>	X <sup>5)</sup>	X <sup>5)</sup>	-	X	-	-	
Windows 7 (64 Bit)	X	X <sup>6)</sup>	X	X	-	X <sup>5)</sup>	X <sup>4)7)</sup>	X <sup>5)</sup>	X <sup>4)7)</sup>	-	X	-	-	
Windows 7 (32 Bit)	X	X <sup>6)</sup>	X	X	X <sup>1)</sup>	X <sup>5)</sup>	X <sup>2)7)</sup>	X <sup>5)</sup>	X <sup>2)7)</sup>	-	X	X <sup>2)</sup>	-	
Windows Vista SP2	X	X <sup>9)</sup>	X	X	X	X <sup>8)</sup>	X	X <sup>8)</sup>	X	X	X	X	-	
Windows Vista SP1	X	X <sup>9)</sup>	X	X	X	X <sup>8)</sup>	X	X <sup>8)</sup>	X	X	X	X	-	
Windows Vista	X	-	X	-	X	-	X	-	X	X	X	X	-	
Windows XP SP3	X	X <sup>9)</sup>	X	X	X	X <sup>8)</sup>	X	X <sup>8)</sup>	X	X	X	X	X	
Windows XP SP2	X	X <sup>9)</sup>	X	X	X	X <sup>8)</sup>	X	X <sup>8)</sup>	X	X	X	X	X	
Windows XP SP1	-	-	X	-	X	-	X	-	X	X	-	X	X	
Windows Server 2016 (64 Bit)	X	X	X	X	-	X	X <sup>7)</sup>	X	X <sup>7)</sup>	-	X	-	-	
Windows Server 2012 R2 (64 Bit)	X	X	X	X	-	X	X <sup>7)</sup>	X	X <sup>7)</sup>	-	X	-	-	
Windows Server 2012 (64 Bit)	X	X <sup>6)</sup>	X	X	-	X	X <sup>7)</sup>	X	X <sup>7)</sup>	-	X	-	-	
Windows Server 2008 R2 SP1 (64 Bit)	X	X	X	X	-	X	X <sup>4)7)</sup>	X	X <sup>4)7)</sup>	-	X	-	-	
Windows Server 2008 R2 (64 Bit)	X	X <sup>6)</sup>	X	X	-	X <sup>5)</sup>	X <sup>4)7)</sup>	X <sup>5)</sup>	X <sup>4)7)</sup>	-	X	-	-	
Windows Server 2008 SP2	X	X <sup>9)</sup>	X	X	X	X <sup>8)</sup>	X	X <sup>8)</sup>	X	X	X	X	-	
Windows Server 2008	X	-	X	X	X	-	X	-	X	X	X	X	-	
Windows Server 2003 R2 SP2	X	-	X	X	X	-	X	-	X	X	X	X	-	
Windows Server 2003 R2 SP1	-	-	X	-	X	-	X	-	X	X	-	X	-	
Windows Server 2003 SP2	-	X <sup>9)</sup>	X	-	X	X <sup>8)</sup>	X	X <sup>8)</sup>	X	X	-	X	-	
Windows Server 2003 SP1	-	-	X	-	X	-	X	-	X	X	-	X	-	
Windows Server 2003	-	-	X	-	X	-	X	-	X	X	-	X	-	
Windows 2000 SP4	-	-	X	-	X	-	X	-	X	X	-	X	X	
Windows 2000 SP3	-	-	X	-	X	-	X	-	X	X	-	X	X	
Windows 2000 SP1/2	-	-	-	-	X	-	X	-	-	X <sup>3)</sup>	X	-	X	X
Windows 2000	-	-	-	-	X	-	-	-	-	X <sup>3)</sup>	X	-	-	X
Windows NT4.0 SP6a	-	-	-	-	X	-	-	-	-	X <sup>3)</sup>	X	-	-	X
Windows 98	-	-	-	-	-	-	-	-	-	-	X	-	-	X
Windows 95	-	-	-	-	-	-	-	-	-	-	X	-	-	X

This entry is from the Service&amp;Support portal of Siemens AG, Siemens Industry Online Support.

The general terms of use ([http://www.siemens.com/terms\\_of\\_use](http://www.siemens.com/terms_of_use)) apply.

<sup>1)</sup> CP5613 FO is released under Windows 7.

<sup>2)</sup> The module is not released for configured mode under Windows 7 with SIMATIC NET CD V8.0.

<sup>3)</sup> only if before a CP5611 A1 was installed (spare part case)

<sup>4)</sup> The module is not released for configured mode under 64 Bit operating systems with SIMATIC NET DVD V8.2 and higher version.

<sup>5)</sup> The module is supported since SIMATIC NET DVD V8.2 SP1.

<sup>6)</sup> The module is supported since SIMATIC NET DVD V12 + HF1.

<sup>7)</sup> The module is not released for configured mode with SIMATIC NET DVD V12 and higher version.

<sup>8)</sup> see Entry-ID: <http://support.automation.siemens.com/WW/view/en/84138725>

<sup>9)</sup> see Entry-ID: <http://support.automation.siemens.com/WW/view/en/103880893>

<sup>10)</sup> from Version 1511 Build 10586