

Module	Article number	Firmware version	Multiport	Released ports
S7-1500 CPUs				
CPU 1511-1 PN	6ES7511-1AK00-0AB0 6ES7511-1AK01-0AB0	V1.1 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1511F-1 PN	6ES7511-1FK00-0AB0 6ES7511-1FK01-0AB0	V1.7 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1513-1 PN	6ES7513-1AL00-0AB0 6ES7513-1AL01-0AB0	V1.1 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1513F-1 PN	6ES7513-1FL00-0AB0 6ES7513-1FL01-0AB0	V1.7 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1515-2 PN	6ES7515-2AM00-0AB0 6ES7515-2AM01-0AB0	V1.5 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1515F-2 PN	6ES7515-2FM00-0AB0 6ES7515-2FM01-0AB0	V1.6 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1516-3 PN/DP	6ES7516-3AN00-0AB0 6ES7516-3AN01-0AB0	V1.1 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1516F-3 PN/DP	6ES7516-3FN00-0AB0 6ES7516-3FN01-0AB0	V1.5 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1517(F)-3 PN/DP	6ES7517-3AP00-0AB0 6ES7517-3FP00-0AB0	V1.6 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1518(F)-4 PN/DP	6ES7518-4AP00-0AB0 6ES7518-4FP00-0AB0	V1.5 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1510SP-1 PN	6ES7510-1DJ00-0AB0 6ES7510-1DJ01-0AB0	V1.6 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1510SP F-1 PN	6ES7510-1SJ00-0AB0 6ES7510-1SJ01-0AB0	V1.7 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1512SP-1 PN	6ES7510-1DK00-0AB0 6ES7510-1DK01-0AB0	V1.6 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1512SP F-1 PN	6ES7512-1SK00-0AB0 6ES7512-1SK01-0AB0	V1.7 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1511C-1 PN	6ES7511-1CK00-0AB0	V1.8 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1512C-1 PN	6ES7512-1CK00-0AB0	V1.8 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1507S	6ES7672-7AC00-0YA0	V1.8 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
CPU 1505S	6ES7672-5AC00-0YA0	V1.8 and higher	Yes	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964

S7-1200 CPUs				
CPU 1211C	6ES7211-1AD30-0XB0	V1.02 and higher	No	All except:
	6ES7211-1AE31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7211-1AE40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.
	6ES7211-1BD30-0XB0	V1.02 and higher	No	All except:
	6ES7211-1BE31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7211-1BE40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.
	6ES7211-1HD30-0XB0	V1.02 and higher	No	All except:
	6ES7211-1HE31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7211-1HE40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.
CPU 1212C	6ES7212-1AD30-0XB0	V1.02 and higher	No	All except:
	6ES7212-1AE31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7212-1AE40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.
	6ES7212-1BD30-0XB0	V1.02 and higher	No	All except:
	6ES7212-1BE31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7212-1BE40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.
	6ES7212-1HD30-0XB0	V1.02 and higher	No	All except:
	6ES7212-1HE31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7212-1HE40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.
CPU 1214C	6ES7214-1AE30-0XB0	V1.02 and higher	No	All except:
	6ES7214-1AG31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7214-1AG40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.
	6ES7214-1BE30-0XB0	V1.02 and higher	No	All except:
	6ES7214-1BG31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7214-1BG40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.
	6ES7214-1HE30-0XB0	V1.02 and higher	No	All except:
	6ES7214-1HG31-0XB0	V3.0 and higher	No	20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964
	6ES7214-1HG40-0XB0	V4.0 and higher	No	Note
		V4.1 and higher	Yes	Port 123 is released in addition in V4.1.2 and higher.

CPU 1214 FC	6ES7214-1AF40-0XB0 6ES7214-1HF40-0XB0	V4.1.2 and higher	Yes	All except: 20, 21, 25, 80, 102, 5001, 34962, 34963 and 34964
CPU 1215C	6ES7215-1AG31-0XB0 6ES7215-1AG40-0XB0	V3.0 and higher	No	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964 Note Port 123 is released in addition in V4.1.2 and higher.
		V4.0 and higher	No	
		V4.1 and higher	Yes	
	6ES7215-1BG31-0XB0 6ES7215-1BG40-0XB0	V3.0 and higher	No	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964 Note Port 123 is released in addition in V4.1.2 and higher.
		V4.0 and higher	No	
		V4.1 and higher	Yes	
6ES7215-1HG31-0XB0 6ES7215-1HG40-0XB0	V3.0 and higher	No	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964 Note Port 123 is released in addition in V4.1.2 and higher.	
	V4.0 and higher	No		
6ES7215-1HG31-0XB0 6ES7215-1HG40-0XB0	V4.0 and higher	No	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964 Note Port 123 is released in addition in V4.1.2 and higher.	
	V4.1 and higher	Yes		
CPU 1215 FC	6ES7215-1AF40-0XB0 6ES7215-1HF40-0XB0	V4.1.2 and higher	Yes	All except: 20, 21, 25, 80, 102, 5001, 34962, 34963 and 34964
CPU 1217C	6ES7217-1AG40-0XB0	V4.0 and higher	No	All except: 20, 21, 25, 80, 102, 123, 5001, 34962, 34963 and 34964 Note Port 123 is released in addition in V4.1.2 and higher.
		V4.1 and higher	Yes	
S7-400 CPUs				
CPU 412-2 PN	6ES7412-2EK06-0AB0	V6.0 and higher	Yes	all
CPU 412-2 PN	6ES7412-2EK07-0AB0	V7.0 and higher	Yes	all
CPU 414-3 PN/DP	6ES7414-3EM05-0AB0	V5.0 and higher	No	all
CPU 414(F)-3 PN/DP	6ES7414-3EM06-0AB0	V6.0 and higher	Yes	all
	6ES7414-3FM06-0AB0			
CPU 414(F)-3 PN/DP	6ES7414-3EM07-0AB0	V7.0 and higher	Yes	all
	6ES7414-3FM07-0AB0			
CPU 416(F)-3 PN/DP	6ES7416-3ER05-0AB0	V5.0 and higher	No	all
	6ES7416-3FR05-0AB0			
CPU 416(F)-3 PN/DP	6ES7416-3ES06-0AB0	V6.0 and higher	Yes	all
	6ES7416-3FS06-0AB0			
CPU 416(F)-3 PN/DP	6ES7416-3ES07-0AB0	V7.0 and higher	Yes	all
	6ES7416-3FS07-0AB0			
CPU 412-5H PN/DP	6ES7412-5HK06-0AB0	V6.0 and higher	Yes	all
CPU 414-5H PN/DP	6ES7414-5HM06-0AB0	V6.0 and higher	Yes	all
CPU 416-5H PN/DP	6ES7416-5HS06-0AB0	V6.0 and higher	Yes	all
CPU 417-5H PN/DP	6ES7417-5HT06-0AB0	V6.0 and higher	Yes	all

CPU 410-5H	6ES7410-5HX08-0AB0	V8.0 and higher	Yes	all
CPU 410 SMART	6ES7410-5HN08-0AB0	V8.1 and higher	Yes	all
S7-300 CPUs				
CPU 314C-2 PN/DP	6ES7314-6EH04-0AB0	V3.3 and higher	Yes	all
CPU 315(F)-2 PN/DP	6ES7315-2EG10-0AB0 6ES7315-2EH13-0AB0 6ES7315-2FH10-0AB0 6ES7315-2FH13-0AB0	up to V2.3.4	No	2000 to 5000
CPU 315(F)-2 PN/DP	6ES7315-2EH14-0AB0 6ES7315-2FJ14-0AB0	V3.1 and higher	Yes	all
CPU 315T-3 PN/DP	6ES7315-7TJ10-0AB0	V3.2 and higher	Yes	all
CPU 317(F)-2 PN/DP	6ES7317-2EK13-0AB0 6ES7317-2FK13-0AB0	uo to V2.3	No	2000 to 5000
CPU 317(F)-2 PN/DP	6ES7317-2EK14-0AB0 6ES7317-2FK14-0AB0	V3.1 and higher	Yes	all
CPU 317T-3 PN/DP	6ES7317-7TK10-0AB0	V3.2 and higher	Yes	all
CPU 317TF-3 PN/DP	6ES7317-7UL10-0AB0	V3.2 and higher	Yes	all
CPU 319(F)-3 PN/DP	6ES7318-3EL00-0AB0 6ES7318-3FL00-0AB0	up to V2.6	No	2000 to 5000
CPU 319(F)-3 PN/DP	6ES7318-3EL00-0AB0 6ES7318-3FL00-0AB0	up to V2.7	No	all
CPU 319(F)-3 PN/DP	6ES7318-3EL01-0AB0 6ES7318-3FL01-0AB0	from V3.2	Yes	all
ET 200 CPUs				
IM 151-8(F) PN/DP CPU	6ES7151-8AB00-0AB0 6ES7151-8FB00-0AB0	up to V2.6	No	2000 to 5000
IM 151-8(F) PN/DP CPU	6ES7151-8AB00-0AB0 6ES7151-8FB00-0AB0	V2.7 and higher	No	all
IM 151-8(F) PN/DP CPU	6ES7151-8AB01-0AB0 6ES7151-8FB01-0AB0	V3.2 and higher	Yes	all
IM 154-8 PN/DP CPU	6ES7154-8AB00-0AB0	up to V2.5	No	2000 to 5000
IM 154-8 PN/DP CPU	6ES7154-8AB01-0AB0	V3.2 and higher	Yes	all
IM 154-8F PN/DP CPU	6ES7154-8FB01-0AB0	V3.2 and higher	Yes	all
IM 154-8FX PN/DP CPU	6ES7154-8FX00-0AB0	V3.2 and higher	Yes	all