SINUMERIK Integrate Create MyHMI /WinCC V15
Supplementary Conditions

In addition to the below-stated supplementary conditions, the supplementary conditions for the specified respectively supported TIA Portal software apply accordingly:

- SIMATIC WinCC Advanced V15

ID	Issue	Description	Workaround
2640586	FANUC SDF display is not supported	The use of a FANUC SDF display in WinCC Runtime is not approved. This screen object is displayed in the editor, but is not supported and cannot be used.	
2630031	Windows theme "Windows Classic" not supported by SINUMERIK Operate	If, for example, SINUMERIK Operate is used for the purpose of displaying an NC operating display in the screen object in the "WinCC extended HMI" configuration, the Windows theme must not be set to "Windows Classic". Otherwise, SINUMERIK Operate will not be properly ended when the WinCC Runtime is ended.	
2583000	Activating the screen keyboard	When a general PC station or a SIMATIC Box PC is used, you must configure the settings for the on-screen keyboard, e.g. under "PC-System_1 > HMI_RT_1 > Runtime settings > Keyboard".	
2572619	Windows Explorer is not supported by the application display	Windows Explorer must not be positioned in the application display screen object in WinCC Runtime.	
1824572	NC alarm text modifications	Changes to standard NC alarm texts in the previous version are not automatically applied to alarm texts in the current version.	These adjustments must be replicated explicitly in the current alarm texts.
1824516	SINUMERIK Operate 1:N selection is not supported by WinCC RT Advanced	If a connection between a PCU 50.5 and several NCUs (1:N) is switched in SINUMERIK Operate, then this change is not applied to the WinCC RT Advanced automatically.	Access to several controllers must be configured in the engineering system independently of SINUMERIK Operate and then switched manually in the WinCC RT Advanced (additionally to the SINUMERIK Operate configuration).
1824504	Objects "NC File Viewer" and "NC File Editor"	The objects "NC File Viewer" and "NC File Editor" are not available in WinCC (NC part program selection and change).	The control "NCPartProgram" can be used to load active part programs.

ID	Issue	Description	Workaround
1824471	Drive data in WinCC	Variables cannot be configured with Drive TAGs from SINUMERIK (no SINAMICS data).	None
1801853	SIMATIC KTPx00F Mobile at SINUMERIK NCU 840D sl	For SIMATIC KTPx00F-Mobile Panel, the communication to the NC of an NCU has been tested and released. This does not include a release of the F functionality of the F panel on a SINUMERIK NCU.	None
1720406	Migration of a SINUMERIK HMI panel with inserted CP	You may insert (plug in) a CP device in the rack (configuration table) of a SINUMERIK HMI panel in STEP 7 V5.x, this is, however, not a suitable or supported configuration option. Such a configuration is not supported and cannot be migrated in TIA Portal.	
1640293	No support for WinCC RT Advanced V11 SP2 with SINUMERIK PCU 50.5	Using WinCC RT Advanced 11.0.2.0 (V11 SP2) in a SINUMERIK PCU 50.5 is not supported. This RT version is listed in the dialog box "Change device/version", but must not be used.	