

		Version des Betriebssystem MS Windows																				
		Win 95	Win 98	Win 98 SE	Win ME	Win NT 3.xx	Win NT 4.0	Win NT 4.0 SP5	Win NT 4.0 SP6	Win 2000	Win 2000 SP2	Win 2000 SP3	Win 2000 SP4	Win XP	Win XP SP1	Win XP SP2	Win XP SP3	Vista	Vista SP1	Vista SP2	Windows 7 (32/64 Bit)	Windows 7 SP1 (32/64 Bit)
Version der S7-200 Software	S7-200 Software Version																					
	STEP 7-Micro/WIN V 1.0	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 1.2	K	NK	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 2.0	K	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 2.11	K	NK	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 2.12.32	K	NK	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 3.01.000	K	K	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 3.02.020	K	K	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 3.1.0.31	K	K	NK	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 3.1.1.6	K	K	NK	NK	NK	NK	K	NK	K*	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 3.1.2.22	K	K	NK	K	NK	NK	K	K	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 3.2.0.105	K	NK	K	K	NK	NK	K	K	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 3.2.0.108	K	NK	K	K	NK	NK	K	K	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V 3.2.1.29	K	NK	K	K	NK	NK	K	K	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V3.2.1.34	K	NK	K	K	NK	NK	K	K	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V3.2.2.11	K	NK	K	K	NK	NK	K	K	NK	K	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V3.2.3.17	K	NK	K	K	NK	NK	NK	K	NK	K	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V3.2.4.27	K	NK	K	K	NK	NK	NK	K	NK	K	NK	NK	NK	K	NK	NK	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V4.0.0.81	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V4.0.1.10	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V4.0.2.29	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V4.0.3	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V4.0.4	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V4.0.5.08	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	NK	NK	NK	NK
	STEP 7-Micro/WIN V4.0.6.35	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	K	NK	NK	NK
	STEP 7-Micro/WIN V4.0.7.10	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	K	K	K	K	NK
	STEP 7-Micro/WIN V4.0.8.06	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	*	K	K	K	K	K	K	K	NK
	STEP 7-Micro/WIN V4.0.9.25	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	*	*	*	*	*	K	*	*	*	K
	S7-200 PC Access V1.0.0	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	NK	K	NK	NK	NK	NK	NK	NK
	S7-200 PC Access V1.0.1	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	NK	K	K	NK	NK	NK	NK	NK
	S7-200 PC Access V1.0.2.26	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	NK	NK	NK	NK
	S7-200 PC Access V1.0.3.35	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	NK	K	NK	NK	NK
S7-200 PC Access V1.0.4.10	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	K	K	K	K	K*	K	NK	NK	NK	
S7-200 PC Access V1.0.5.06	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	K	*	K	K	K	K	K	K	K	NK	
S7-200 PC Access V1.0.6.25	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	NK	*	*	*	*	*	K	*	*	*	K	

K = Kompatibel
* = kein Systemtest

NK = nicht Kompatibel