Load Cells

Load cell accessories

SIWAREX EB extension box

Overview



The EB extension box is used to lengthen load cell connecting cables.

Load cells can be connected in 4-wire or 6-wire systems. The cable connection to the weighing module or to the JB junction box must always be implemented in 6-wire systems. The 7MH4 702-8AG or

...-8ÅF SIWAREX connection cable is recommended for this purpose. If load cell cables are extended to a JB junction box, the M16 x 1.5 cable glands on the box must be replaced. The following is required for each load cell:

• 1 EMC cable gland M20 x 1.5


• 1 extension M16 x 1.5 male thread to M20 x 1.5 female thread.

Design

The EB extension box consists of a housing made of die-cast aluminum. It is protected against dust and spray water according to IP66. The cables are fed in through metric EMC cable glands and laid in spring-loaded terminals. A vibration-resistant and maintenance-free connection is achieved through the use of spring-loaded terminals. For connecting load cells in a 4-wire system, two bridge elements are inserted for feedback of the sense signal.

Connection examples


Connecting one load cell



LC: Load cell

Design (Continued)

Connecting multiple load cells



LC: Load cell

Selection and ordering data


Article No.	
Accessories	
SIWAREX EB extension box, aluminum enclosure For extending the connecting cable of load cells	7MH4710-2AA
Cable (optional)	
Cable Li2Y 1 x 2 x 0.75 ST + 2 x (2 x 0.34 ST) – CY	
For connecting SIWAREX electronic weighing systems to junction box (JB), extension box (EB) and Ex inter- face or between two extension boxes. For permanent installation. Occasional bending is pos- sible. External diameter: approx. 10.8 mm (0.43 inch) Permissible ambient temperature -40 +80 °C (-40 +176 °F) Sold by the meter.	
Sheath color: orange	7MH4702-8AG
For hazardous atmospheres. Sheath color: blue.	7MH4702-8AF

Technical specifications

Cable glands	
Of load cell cable	M16 × 1.5
Of signal cable	M20 × 1.5
Permissible ambient temperature	
During operation	-30 +85 °C (-22 185 °F)
• During operation for legal-for-trade weigh- ing machines	-10 +40 °C (14 104 °F)
During transportation and storage	-40 +90 °C (-40 194 °F)
Degree of protection acc. to EN 60529	IP66
Vibration resistance of terminals to DIN VDE 0611 11/77	12 Hz and 50 Hz, amplitude 1 mm
Insulation resistance of the terminals	$\geq 10^{12} \Omega$
Dimensions (W \times H \times D) in mm	80 × 75 × 57

SIWAREX EB extension box

Dimensional drawings



SIWAREX EB extension box (7MH4 710-2AA), dimensions in mm (inch)