



**IEC 60601-1**  
**Medical electrical equipment**  
**Part 1: General requirements for basic safety and essential performance**

**Report Reference No.....:** 16TH0062-60601-1\_2nd\_0  
**Date of issue .....** 2016-06-27  
**Total number of pages .....** 149

**CB Testing Laboratory.....:** Bureau Veritas Consumer Products Services Germany GmbH  
**Address .....** Businesspark A96, 86842 Türkheim, GERMANY

**Applicant's name.....:** Siemens AG Österreich  
**Address .....** Siemensstr. 90 - 92; 1210 Wien; AUSTRIA

**Test specification:**  
**Standard .....** IEC 60601-1:1988 + A1:1991 + A2:1995  
**Test procedure.....:** Test Report  
**Non-standard test method.....:** N/A

**Test Report Form No.....:** IEC60601\_1C\_II  
**Test Report Form Originator .....** Underwriters Laboratories Inc.  
**Master TRF .....** Dated 2011-11



Copyright © 2011 IEC System for Conformity Testing and Certification of Electrical Equipment (IECEE), Geneva, Switzerland. All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo shall be removed

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

**Test item description .....** : Power Supply Unit (DIN Rail)  
**Trade Mark.....** : SIEMENS  
**Manufacturer .....** : LECO GmbH, Schloßhofer Str. 4/4/13; A-1210 Wien; AUSTRIA  
**Model/Type reference.....** : 6EP4333-0SB00-0YA0; 6EP4436-0SB00-0YA0  
**Ratings.....** : 6EP4333-0SB00-0YA0:  
Input: 120 - 230 V; 2,5 - 1,4 A; 50 - 60 Hz  
110 - 220 Vdc; 1,2 - 0,7 A  
Output: 24 V; 5 A  
6EP4436-0SB00-0YA0:  
Input: 3 AC 400 - 500 V; 1,2 A; 50 - 60 Hz  
Output: 24 V; 20 A

Testing procedure and testing location:	
<input checked="" type="checkbox"/> <b>CB Testing Laboratory:</b>	<b>Bureau Veritas Consumer Products Services Germany GmbH</b>
<b>Testing location/ address.....:</b>	<b>Businesspark A96, 86842 Türkheim, GERMANY</b>
<input type="checkbox"/> <b>Associated CB Test Laboratory:</b>	
<b>Testing location/ address.....:</b>	
<b>Tested by (name + signature) ..:</b>	<b>Thomas Ruffer</b> 
<b>Approved by (+ signature) .....</b>	<b>Max Gebuhr</b> 
<input type="checkbox"/> <b>Testing procedure: TMP</b>	
<b>Tested by (name + signature) ..:</b>	
<b>Approved by (+ signature) .....</b>	
<b>Testing location/ address.....:</b>	
<input type="checkbox"/> <b>Testing procedure: WMT</b>	
<b>Tested by (name + signature) ..:</b>	
<b>Witnessed by (+ signature) .....</b>	
<b>Approved by (+ signature) .....</b>	
<b>Testing location/ address.....:</b>	
<input type="checkbox"/> <b>Testing procedure: SMT</b>	
<b>Tested by (name + signature) ..:</b>	
<b>Approved by (+ signature) .....</b>	
<b>Supervised by (+ signature).....:</b>	
<b>Testing location/ address.....:</b>	
<input type="checkbox"/> <b>Testing procedure: RMT</b>	
<b>Tested by (name + signature) ..:</b>	
<b>Approved by (+ signature) .....</b>	
<b>Supervised by (+ signature).....:</b>	
<b>Testing location/ address.....:</b>	