Supplementary components

Displays

SITRANS RD300

Overview



The SITRANS RD300 is a panel mount remote digital display for process instrumentation and acts as a multi-purpose, easy to use, rate/totalizer ideal for flow rate, total, and control applications.

Benefits

- Easy setup and programming via front panel buttons or using free RD software available via USB drive
- Display readable in sunlight
- · Input: accepts current and voltage
- Single or dual 24 V DC transmitter power supply
- · Serial communication using built in protocol or Modbus RTU
- Supports up to 8 relays and 8 digital I/O for process control and alarming
- 32-Point linearization, square root or exponential linearization
- Multi-pump alternation control
- Supports total, grand total or non-resettable grand total
- 9-digit totalizer with total overflow feature
- Large dual-line, 6-digit display
- · Configure, monitor, and datalog from a PC
- Dual-input option with math functions: addition, difference, average, multiplication, division, minimum, maximum, weighted average, ratio, concentration

Application

The RD300 is a remote display for level, flow, pressure, weighing, and other process instruments. This display also acts as a multi-purpose, easy to use rate/totalizer ideal for flow rate, total, and control applications.

Data can be remotely collected, logged and presented on your local computer using the free RD software available via USB drive

The display accepts a single or dual input of current and voltage. This makes the RD300 an ideal fit for use with most field instruments

The RD300 can be set up as a standard panel mount, or combined with optional enclosures to allow it to house up to 6 displays.

 Key Applications: tank farms, pump alternation control, local or remote display of level, flow, pressure and weighing instrument values, PC monitoring and data logging with RD Software

Supplementary components

. Displays

SITRANS RD300


Technical specifications

•		
Mode of operation		
Measuring principle	Analog to digital conversion	
Measuring points	1 or 2 instruments	
Input		
Measuring range		
Current	4 20 mA, 0 20 mA	
Voltage	0 V DC +10 V DC, 1 5 V, 0 5 V	
Output signal		
Output	4 20 mA (optional)Modbus RTU	
Relays	2 or 4 SPDT (Form C) internal and/or 4 SPST (Form A) external; rated 3 A at 30 V DC and 125/250 V AC resis- tive load; 1/14 HP (50 W) at 125/250 V AC for inductive loads (optional)	
Communications	RS 232 with Modbus RTU RS 422/485 with Modbus RTU USB configuration and monitoring port	
Accuracy		
4 20 mA optional output	± 0.1 % FS	
	± 0.004 mA	
Process input	± 0.05 % of span ± 1 count, square root: 10 100 % FS	
Rated operating conditions		
Ambient conditions • Storage temperature range • Operating temperature range	-40 +85 °C (-40 +185 °F) -40 +65 °C (-40 +149 °F)	
Design		
Weight	269 g (9.5 oz) (including options)	
Material (enclosure)	1/8 DIN, high impact plastic, UL94V-0, color: gray Optional plastic, steel and stainless steel (Type 304, EN 1.4301) NEMA 4 enclosures	
Degree of protection	Type 4X, NEMA 4X, IP65 (front cover); panel gasket provided	

Electrical connection		
mA output signal	2-core copper conductor, twisted, shielded, 0.82 3.30 mm ² (18 12 AWG), Belden 8 760 or equivalent is acceptable	
Electrical connection and relay connection	Copper conductor according to local requirements, rated 3 A at 250 V AC	
Power supply		
Input voltage option	85 265 V AC, 50/60 Hz; 90 265 V DC, 20 W max. or jumpe selectable 12/24 V DC ± 10 %, 15 W max.	
Transmitter power supply	Terminals P+ & P-: 24 V DC ± 10 %, 12/24 V DC powered models selectable for 24, 10, or 5 V DC supply (internal jumper J4), 85 265 V AC models rated at 200 mA max, 12/24 V DC powered models rated at 100 mA max., at 50 mA max. for 5 or 10 V DC supply.	
External loop power supply	35 V DC max.	
Output loop resistance	 24 V DC, 10 700 Ω max. 35 V DC (external), 100 1 200 Ω max. 	
Displays and controls		
Main display	0.6 inch (15 mm) high, red LEDs	
Second display	0.46 inch (12 mm) high, red LEDs, 6-digits: each (-99 999 999 999)	
Memory	Non-volatile Stores settings for minimum of 10 years if power is lost	
Programming	Primary: front panel Secondary: Meter Copy or PC with SITRANS RD Software	
Certificates and approvals	CE, UL, _C UL	
Options		
Enclosures	Plastic, steel and stainless steel (Type 304, EN 1.4301) NEMA 4 and 4X enclosures	


Selection and ordering data

Supplementary components



Operating Instructions All literature is available to download for free, in a range of languages, at	
in a range of languages, at	
http://www.siemens.com/ processinstrumentation/documentation	
Accessories	
DIN-Rail Mounting Kit 7ML1930-6AB	
4 Relays Expansion Module 7ML1930-6AC	
4 Digital I/O Module 7ML1930-6AD	
Dual output 4 20 mA expansion module for dual input meter 7ML1930-6AP	
Meter Copy Cable 7ML1930-6AE	
RD300 RS 232 Serial Adapter 7ML1930-6AF	
RD300 RS 422/485 Serial Adapter 7ML1930-6AG	
RD300 USB Serial Adapter 7ML1930-6AJ	
USB to RS 232 Converter 7ML1930-6AK	
RS 232 to RS 422/485 isolated converter 7ML1930-1BU	
RS 232 to RS 422/485 non-isolated converter 7ML1930-1BV	
USB to RS 422/485 isolated converter 7ML1930-1BX	
USB to RS 422/485 non-isolated converter 7ML1930-1BY	
Snubber 7ML1930-6AL	
Plastic enclosure	
For 1 meter 7ML1930-6AM	
For 2 meters 7ML1930-6AN	
For 4 meters 7ML1930-1CK	
For 5 meters 7ML1930-1CL	
For 6 meters 7ML1930-1CM	

Dimensional drawings



SITRANS RD300, dimensions in mm (inch)

Supplementary components

Displays


SITRANS RD300

Circuit diagrams


Connector labeling for fully loaded single input meter




Transmitter powered by external supply or self-powered



Transmitter powered by internal supply



Voltage Input Connections



SITRANS RD300 connections