

Siemens Radio Interference Suppression Filter suitable for use with SIMOREG DC-Master 6RA70

| | |
|----------------------|--|
| Rated Voltage | 3AC 520 V |
| Rated Frequency | 50/60 Hz |
| Ambient Temperature | ta 40°C |
| Degree of protection | IP20 (EN 60529), IP00 for I \geq 200 A |
| Standard | EN 133200 |
| Approbation | UL 1283, CSA22.2 No.8 1986 |

| Rated current Radio Interference Suppression Filters | Radio Interference Suppression Filters | Leakage current | Terminal cross- section mm ² | weight approx. | Dimensions HxBxT | | |
|--|---|--------------------|--|-------------------|------------------|-----|------|
| A | Type | mA | Holes for M . | kg | mm | mm | mm |
| 8 | 4EF1510-1AA10 | 12 | 4 | 0,58 | 36 | 165 | 51,4 |
| 16 | 4EF1510-2AA10 | 14 | 4 | 0,9 | 70 | 231 | 46,4 |
| 25 | 4EF1510-3AA10 | 14 | 4 | 1,1 | 83 | 231 | 46,4 |
| 36 | 4EF1510-4AA10 | 14 | 10 | 1,75 | 90 | 265 | 57 |
| 50 | 4EF1510-5AA10 | 14 | 10 | 1,75 | 90 | 265 | 57 |
| 66 | 4EF1510-6AA10 | 14 | 16 | 2,7 | 141,5 | 265 | 58 |
| 90 | 4EF1510-7AA10 | 16 | 35 | 4,2 | 135 | 290 | 80 |
| 120 | 4EF1510-8AA10 | 16 | 35 | 4,9 | 150 | 290 | 90 |
| 150 | 4EF1512-7AA10 | 16 | 50 | 5,3 | 150 | 326 | 90 |
| 220 | 4EF1511-0AA10 | 16 | 95 | 11,5 | 220 | 430 | 110 |
| 250 | 4EF1511-1AA10 | 21 | M8 | 5 | 110 | 270 | 140 |
| 320 | 4EF1511-2AA10 | 21 | M10 | 7,2 | 116 | 320 | 140 |
| 400 | 4EF1511-3AA10 | 21 | M10 | 7,5 | 116 | 320 | 140 |
| 600 | 4EF1511-4AA10 | 21 | M10 | 7,8 | 116 | 320 | 140 |
| 1000 | 4EF1511-5AA10 | 40 | M12 | 18,5 | 140 | 410 | 210 |
| 1600 | 4EF1511-6AA10 | 40 | 2 x M12 | 24,5 | 140 | 490 | 210 |