

Measured Components of PN-Rea V3.0 (ID11)

Component		Type	MLFB	Version
IO controller	S7-300	CPU 315-2DP	6ES7 315-2AG10-0AB0	V 2.0
		CP 343-1	6GK7 343-1EX21-0XE0	V 1.1
		CPU 315-2 PN/DP	6ES7 315-2EG10-0AB0	V 2.3
		CPU 317-2 DP	6ES7 317-2AJ10-0AB0	V 2.1
		CPU 317-2PN/DP	6ES7 317-2EJ10-0AB0	V 2.3
		CPU 319-3PN/DP	6ES7 318-3EL00-0AB0	V 2.4
	S7-400	CPU 414-2DP	6ES7 414-2XG04-0AB0	V 4.0
		CP 443-1 Adv.	6GK7 443-1EX40-0XE0	V 2.4
		CPU 414-3PN/DP	6ES7 414-3EK05-0AB0	V 5.0
		CPU 416-3PN/DP	6ES7 416-3EM05-0AB0	V 5.0
	PC	Linux based PC	Rack-PC-840-V2	Suse Linux with RTAI (realtime extension)
		CP 1616	6GK1 161-6AA0	V 2.0
Network topology	switch	SCALANCE X224	6GK5 108-0BA00-2AA3	
	Access Point	SCALANCE W 788-1RR	6GK5 788-1SR00-2AA6	V 2.4
	Client module	SCALANCE W747-1RR	6GK5 747-1SR00-2AA6	V 2.4
	ET200S	IM151-3	6ES7 151-3AA20-0AB0	
		I/O module (4 DI)	6ES7 131-4BD01-0AA0	
		I/O module (4 DO)	6ES7 132-4BD01-0AA0	
Network load	PG	PC with STEP 7	6ES7 710..	
STEP 7		V5.4 SP1		