

SIMATIC S7-1200, Digital I/O SM 1223, 16 DI/16 DO, 16 DI 24 V DC, Sink/Source, 16 DO, transistor 0.5 A



General information

Product type designation	SM 1223, DI 16x24 V DC, DQ 16x24 V DC
--------------------------	---------------------------------------

Supply voltage

Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V

Input current

from backplane bus 5 V DC, max.	185 mA
---------------------------------	--------

Digital inputs

- | | |
|---|-------------------|
| <ul style="list-style-type: none"> from load voltage L+ (without load), max. | 4 mA; per channel |
|---|-------------------|

Output voltage

Power supply to the transmitters

- | | |
|---|-----|
| <ul style="list-style-type: none"> present | Yes |
|---|-----|

Power loss

Power loss, typ.	4.5 W
------------------	-------

Digital inputs

Number of digital inputs	16
--------------------------	----

• in groups of	2
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	16
horizontal installation	
— up to 40 °C, max.	16
— up to 50 °C, max.	16
vertical installation	
— up to 40 °C, max.	16
Input voltage	
• Type of input voltage	DC
• Rated value (DC)	24 V
• for signal "0"	5 V DC at 1 mA
• for signal "1"	15 V DC at 2.5 mA
Input current	
• for signal "0", max. (permissible quiescent current)	1 mA
• for signal "1", min.	2.5 mA
• for signal "1", typ.	4 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
for interrupt inputs	
— parameterizable	Yes
Cable length	
• shielded, max.	500 m
• unshielded, max.	300 m
Digital outputs	
Number of digital outputs	
• in groups of	1
Short-circuit protection	No; to be provided externally
Limitation of inductive shutdown voltage to	L+ (-48 V)
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• on lamp load, max.	5 W
Output voltage	
• Rated value (DC)	24 V
• for signal "0", max.	0.1 V; with 10 kOhm load
• for signal "1", min.	20 V DC

Output current	
• for signal "1" rated value	0.5 A
• for signal "1" permissible range, max.	0.5 A
• for signal "0" residual current, max.	10 µA
Output delay with resistive load	
• "0" to "1", max.	50 µs
• "1" to "0", max.	200 µs
Total current of the outputs (per group)	
horizontal installation	
— up to 50 °C, max.	8 A; Current per mass
Relay outputs	
Switching capacity of contacts	
— with inductive load, max.	0.5 A
— on lamp load, max.	5 W
— with resistive load, max.	0.5 A
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes
Diagnostics indication LED	
• for status of the inputs	Yes
• for status of the outputs	Yes
Potential separation	
Potential separation digital inputs	
• between the channels, in groups of	2
Potential separation digital outputs	
• between the channels, in groups of	1
• between the channels and backplane bus	500 V AC
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
Marine approval	Yes

Ambient conditions

Free fall

- Fall height, max. 0.3 m; five times, in product package

Ambient temperature during operation

- min. -20 °C
- max. 60 °C
- horizontal installation, min. -20 °C
- horizontal installation, max. 60 °C
- vertical installation, min. -20 °C
- vertical installation, max. 50 °C
- permissible temperature change 5°C to 55°C, 3°C / minute

Ambient temperature during storage/transportation

- min. -40 °C
- max. 70 °C

Air pressure acc. to IEC 60068-2-13

- Storage/transport, min. 660 hPa
- Storage/transport, max. 1 080 hPa

Relative humidity

- Operation at 25 °C without condensation, max. 95 %

Connection method

required front connector Yes

Mechanics/material

Enclosure material (front)

- Plastic Yes

Dimensions

Width 70 mm

Height 100 mm

Depth 75 mm

Weights

Weight, approx. 310 g

last modified: 10/09/2020