

SIMATIC S7-1200F, CPU 1214 FC, compact CPU, DC/DC/relay, onboard I/O: 14 DI 24 V DC; 10 DO relay 2 A; 2 AI 0-10 V DC, Power supply: DC 20.4-28.8V DC, Program/data memory 125 KB



### General information

Product type designation	CPU 1214FC DC/DC/Relay
Firmware version	V4.2
Engineering with	
<ul style="list-style-type: none"> <li>Programming package</li> </ul>	STEP 7 V14 or higher

### Supply voltage

Rated value (DC)	
<ul style="list-style-type: none"> <li>24 V DC</li> </ul>	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Load voltage L+	
<ul style="list-style-type: none"> <li>Rated value (DC)</li> <li>permissible range, lower limit (DC)</li> <li>permissible range, upper limit (DC)</li> </ul>	24 V 20.4 V 28.8 V

### Input current

Current consumption, max.	1 500 mA; max. with all expansion accessories
Inrush current, max.	12 A; at 28.8 V DC
$I^2t$	0.5 A <sup>2</sup> s

Output current	
for backplane bus (5 V DC), max.	1 600 mA; Max. 5 V DC for SM and CM
Encoder supply	
24 V encoder supply	
• 24 V	L+ minus 4 V DC min.
Power loss	
Power loss, typ.	12 W
Memory	
Work memory	
• integrated	125 kbyte
• expandable	No
Load memory	
• integrated	4 Mbyte
• Plug-in (SIMATIC Memory Card), max.	with SIMATIC memory card
Backup	
• present	Yes
• maintenance-free	Yes
• without battery	Yes
CPU processing times	
for bit operations, typ.	0.08 µs; / instruction
for word operations, typ.	1.7 µs; / instruction
for floating point arithmetic, typ.	2.3 µs; / instruction
CPU-blocks	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used
OB	
• Number, max.	Limited only by RAM for code
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	10 kbyte
Flag	
• Number, max.	8 kbyte; Size of bit memory address area
Local data	
• per priority class, max.	16 kbyte; Priority class 1 (program cycle): 16 KB, priority class 2 to 26: 6 KB
Address area	
Process image	
• Inputs, adjustable	1 kbyte
• Outputs, adjustable	1 kbyte

Hardware configuration	
Number of modules per system, max.	3 comm. modules, 1 signal board, 8 signal modules
Time of day	
Clock	
<ul style="list-style-type: none"> <li>• Hardware clock (real-time)</li> <li>• Backup time</li> <li>• Deviation per day, max.</li> </ul>	Yes 480 h; typical; 12 days min. at 40 °C ±60 s per month
Digital inputs	
Number of digital inputs	14
<ul style="list-style-type: none"> <li>• of which inputs usable for technological functions</li> </ul>	6; HSC (High Speed Counting)
Source/sink input	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	14; 14 inputs at 55 °C horizontal or 45 °C vertical
Input voltage	
<ul style="list-style-type: none"> <li>• Rated value (DC)</li> <li>• for signal "0"</li> <li>• for signal "1"</li> </ul>	24 V; DC at 4 mA nominal 5 V DC at 1 mA 15 V DC at 2.5 mA
Input current	
<ul style="list-style-type: none"> <li>• for signal "1", typ.</li> </ul>	4 mA; nominal
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	0.1 / 0.2 / 0.4 / 0.8 / 1.6 / 3.2 / 6.4 / 10.0 / 12.8 / 20.0 µs; 0.05 / 0.1 / 0.2 / 0.4 / 0.8 / 1.6 / 3.2 / 6.4 / 10.0 / 12.8 / 20.0 ms
— at "0" to "1", min.	0.1 µs
— at "0" to "1", max.	20 ms
for interrupt inputs	
— parameterizable	Yes
for technological functions	
— parameterizable	Yes; Single phase: 3 @ 100 kHz & 3 @ 30 kHz, differential: 3 @ 80 kHz & 3 @ 30 kHz
Cable length	
<ul style="list-style-type: none"> <li>• shielded, max.</li> <li>• unshielded, max.</li> </ul>	500 m; 50 m for technological functions 150 m; for technological functions: No
Digital outputs	
Number of digital outputs	10
Relay outputs	
<ul style="list-style-type: none"> <li>• Number of relay outputs</li> </ul>	10
Analog inputs	
Number of analog inputs	2

<b>Input ranges</b>	
• Voltage	Yes
<b>Input ranges (rated values), voltages</b>	
• 0 to +10 V	Yes
— Input resistance (0 to 10 V)	≥100k ohms
<b>Cable length</b>	
• shielded, max.	100 m; twisted and shielded
<b>Analog outputs</b>	
Number of analog outputs	0
<b>Output ranges, current</b>	
• 0 to 20 mA	Yes
<b>Analog value generation for the inputs</b>	
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	10 bit
• Integration time, parameterizable	Yes
• Conversion time (per channel)	625 μs
<b>Encoder</b>	
<b>Connectable encoders</b>	
• 2-wire sensor	Yes
<b>1. Interface</b>	
Interface type	PROFINET
Isolated	Yes
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
<b>Interface types</b>	
• RJ 45 (Ethernet)	Yes
• Number of ports	1
• integrated switch	No
<b>Protocols</b>	
• PROFINET IO Controller	Yes
• PROFINET IO Device	Yes
• SIMATIC communication	Yes
• Open IE communication	Yes
• Web server	Yes
• Media redundancy	No
<b>PROFINET IO Controller</b>	
• Transmission rate, max.	100 Mbit/s
<b>Services</b>	
— PG/OP communication	Yes

— Isochronous mode	No
— IRT	No
— MRP	No
— MRPD	No
— PROFINergy	No
— Prioritized startup	Yes
— Number of IO devices with prioritized startup, max.	16
— Number of connectable IO Devices, max.	16
— Number of connectable IO Devices for RT, max.	16
— of which in line, max.	16
— Activation/deactivation of IO Devices	Yes
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8
— Updating time	The minimum value of the update time also depends on the communication component set for PROFINET IO, on the number of IO devices and the quantity of configured user data.

#### PROFINET IO Device

##### Services

— PG/OP communication	Yes
— Isochronous mode	No
— IRT	No
— MRP	No
— MRPD	No
— PROFINergy	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	2

#### Protocols

Supports protocol for PROFINET IO	Yes
PROFIBUS	Yes; CM 1243-5 (master) or CM 1242-5 (slave) required
AS-Interface	Yes; CM 1243-2 required
<b>Protocols (Ethernet)</b>	
• TCP/IP	Yes
• DHCP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
<b>SIMATIC communication</b>	
• S7 routing	Yes
<b>Open IE communication</b>	

<ul style="list-style-type: none"> <li>• TCP/IP <ul style="list-style-type: none"> <li>— Data length, max.</li> </ul> </li> <li>• ISO-on-TCP (RFC1006) <ul style="list-style-type: none"> <li>— Data length, max.</li> </ul> </li> <li>• UDP <ul style="list-style-type: none"> <li>— Data length, max.</li> </ul> </li> </ul>	<p>Yes</p> <p>8 kbyte</p> <p>Yes</p> <p>8 kbyte</p> <p>Yes</p> <p>1 472 byte</p>
<b>Web server</b>	
<ul style="list-style-type: none"> <li>• supported</li> <li>• User-defined websites</li> </ul>	<p>Yes</p> <p>Yes</p>
<b>Further protocols</b>	
<ul style="list-style-type: none"> <li>• MODBUS</li> </ul>	<p>Yes</p>
<b>Communication functions</b>	
<b>S7 communication</b>	
<ul style="list-style-type: none"> <li>• supported</li> <li>• as server</li> <li>• as client</li> <li>• User data per job, max.</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>See online help (S7 communication, user data size)</p>
<b>Number of connections</b>	
<ul style="list-style-type: none"> <li>• overall</li> </ul>	<p>16; dynamically</p>
<b>Test commissioning functions</b>	
<b>Status/control</b>	
<ul style="list-style-type: none"> <li>• Status/control variable</li> <li>• Variables</li> </ul>	<p>Yes</p> <p>Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters</p>
<b>Forcing</b>	
<ul style="list-style-type: none"> <li>• Forcing</li> </ul>	<p>Yes</p>
<b>Diagnostic buffer</b>	
<ul style="list-style-type: none"> <li>• present</li> </ul>	<p>Yes</p>
<b>Traces</b>	
<ul style="list-style-type: none"> <li>• Number of configurable Traces</li> <li>• Memory size per trace, max.</li> </ul>	<p>2</p> <p>512 kbyte</p>
<b>Integrated Functions</b>	
Number of counters	6
Counting frequency (counter) max.	100 kHz
Frequency measurement	Yes
controlled positioning	Yes
Number of position-controlled positioning axes, max.	8
Number of positioning axes via pulse-direction interface	Up to 4 with SB 1222
PID controller	Yes
Number of alarm inputs	4

## EMC

### Interference immunity against discharge of static electricity

- |   |      |
|---|------|
| • Interference immunity against discharge of static electricity acc. to IEC 61000-4-2 | Yes  |
| — Test voltage at air discharge   | 8 kV |
| — Test voltage at contact discharge   | 6 kV |

### Interference immunity to cable-borne interference

- |  |     |
|--|-----|
| • Interference immunity on supply lines acc. to IEC 61000-4-4  | Yes |
| • Interference immunity on signal cables acc. to IEC 61000-4-4 | Yes |

### Interference immunity against voltage surge

- |   |     |
|---|-----|
| • Interference immunity on supply lines acc. to IEC 61000-4-5 | Yes |
|---|-----|

### Interference immunity against conducted variable disturbance induced by high-frequency fields

- |  |     |
|--|-----|
| • Interference immunity against high-frequency radiation acc. to IEC 61000-4-6 | Yes |
|--|-----|

### Emission of radio interference acc. to EN 55 011

- |   |  |
|---|--|
| • Limit class A, for use in industrial areas  | Yes; Group 1   |
| • Limit class B, for use in residential areas | Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011 |

## Standards, approvals, certificates

- |                       |     |
|-----------------------|-----|
| CE mark               | Yes |
| UL approval           | Yes |
| cULus                 | Yes |
| FM approval           | Yes |
| RCM (formerly C-TICK) | Yes |
| KC approval           | Yes |
| Marine approval       | Yes |

### Highest safety class achievable in safety mode

- |  |       |
|--|-------|
| • Performance level according to ISO 13849-1 | PLe   |
| • SIL acc. to IEC 61508                      | SIL 3 |

## Ambient conditions

### Ambient temperature during operation

- |                                 |       |
|---------------------------------|-------|
| • min.                          | 0 °C  |
| • max.                          | 55 °C |
| • horizontal installation, min. | 0 °C  |
| • horizontal installation, max. | 55 °C |
| • vertical installation, min.   | 0 °C  |
| • vertical installation, max.   | 45 °C |

### Ambient temperature during storage/transportation

- |        |        |
|--------|--------|
| • min. | -40 °C |
|--------|--------|

• max.	70 °C
<b>Air pressure acc. to IEC 60068-2-13</b>	
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 139 hPa
<b>Relative humidity</b>	
• Operation, max.	95 %; no condensation
<b>Vibrations</b>	
• Vibration resistance during operation acc. to IEC 60068-2-6	2 g (m/s <sup>2</sup> ) wall mounting, 1 g (m/s <sup>2</sup> ) DIN rail
• Operation, tested according to IEC 60068-2-6	Yes
<b>Shock testing</b>	
• tested according to IEC 60068-2-27	Yes; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms
<b>Pollutant concentrations</b>	
• SO <sub>2</sub> at RH < 60% without condensation	SO <sub>2</sub> : < 0.5 ppm; H <sub>2</sub> S: < 0.1 ppm; RH < 60% condensation-free
<b>Configuration</b>	
<b>Programming</b>	
Programming language	
— LAD	Yes; incl. failsafe
— FBD	Yes; incl. failsafe
— SCL	Yes
<b>Know-how protection</b>	
• User program protection/password protection	Yes
• Copy protection	Yes
• Block protection	Yes
<b>Cycle time monitoring</b>	
• adjustable	Yes
<b>Dimensions</b>	
Width	110 mm
Height	100 mm
Depth	75 mm
<b>Weights</b>	
Weight, approx.	435 g
<b>last modified:</b>	11/20/2020