


ET 200AL

Interface modules PROFIBUS DP	Order number
Interface module IM157-1 DP	6ES7157-1AA00-0AB0



Interfaces	Order number
------------	--------------

X1 DP1 (M12 pin)

Non-assembled connectors

PROFIBUS M12 connector 180° with socket insert	6GK1905-0EB00
PROFIBUS M12 connector fast connect 180° with socket insert	6GK1905-0EB10
PROFIBUS M12 connector, angled, with socket insert	3RK1902-1DA00


Non-assembled cables

PROFIBUS FC cable		
- FC Standard Cable		6XV1830-0EH10
- FC Trailing Cable		6XV1830-3EH10
- FC Food Cable (PE sheath)		6XV1830-0GH10
- FC Robust Cable (PUR sheath)		6XV1830-0JH10
- FC FRNC Cable (FRNC sheath)		6XV1830-0LH10
- FC Underground Cable		6XV1830-3FH10
- Festoon Cable GP (PVC sheath)		6XV1830-3GH10
- FC Flexible Cable GP (PUR sheath)		6XV1831-2K

Pre-assembled

PROFIBUS M12 connecting cable, trailable, pre-assembled at both ends with PROFIBUS M12 connectors 180° (one end socket, one end pin)	0,3 m	6XV1830-3DE30
	0,5 m	6XV1830-3DE50
	1,0 m	6XV1830-3DH10
	1,5 m	6XV1830-3DH15
	2,0 m	6XV1830-3DH20

Interface modules PROFINET IO	Order number
Interface module IM157-1 PN	6ES7157-1AB00-0AB0



Interfaces	Order number
------------	--------------

X1 P1R PN LAN (M12 socket)

Non-assembled connectors

PROFINET M12 plug, d-coded with short assembly times due to their insulation- and displacement technology method, 180°		
- 1 piece per pack		6GK1901-0DB10-6AA0
- 8 pieces per pack		6GK1901-0DB10-6AA8
PROFINET M12 plug, d-coded with FastConnect connecting method, 180°		
- 1 piece per pack		6GK1901-0DB20-6AA0
- 8 pieces per pack		6GK1901-0DB20-6AA8
PROFINET M12 plug, d-coded, angled		3RK1902-2DA00

Non-assembled cables

PROFINET FC cable		
- FC TP Standard Cable		6XV1840-2AH10
- FC TP Trailing Cable		6XV1840-3AH10
- FC TP Trailing Cable GP		6XV1870-2D
- FC TP Marine Cable		6XV1840-4AH10
- FC TP Torsion Cable		6XV1870-2F
- FC TP Flexible Cable GP (PVC sheath)		6XV1870-2B
- FC TP FRNC Cable (FRNC sheath)		6XV1871-2F
- FC TP Food Cable (PE sheath)		6XV1871-2L
- FC TP Festoon Cable GP (PVC sheath)		6XV1871-2S

Pre-assembled cables

	3,0 m	6XV1830-3DH30			
	5,0 m	6XV1830-3DH50			
	10,0 m	6XV1830-3DN10			
	15,0 m	6XV1830-3DN15			
PROFIBUS M12 connecting cable, trailable, pre-assembled at both ends with PROFIBUS M12 connectors, angled (one end socket, one end pin)	1,5 m	6XV1830-3DH15-0SB0 ¹⁾			
	2,0 m	6XV1830-3DH20-0SB0 ¹⁾			
	3,0 m	3RK1902-1NB30			
	5,0 m	3RK1902-1NB50			
	10,0 m	3RK1902-1NC10			
	15,0 m	6XV1830-3DN15-0SB0 ¹⁾			
M12 bus termination connector PROFIBUS, socket insert		6GK1905-0ED00			
X1 DP2 (M12 socket)					
Non-assembled connectors					
PROFIBUS M12 connector 180° with pin insert		6GK1905-0EA00			
PROFIBUS M12 connector fast connect 180° with pin insert		6GK1905-0EA10			
PROFIBUS M12 connector, angled, with pin insert		3RK1902-1BA00			
Non-assembled cables					
PROFIBUS FC cable					
- FC Standard Cable		6XV1830-0EH10			
- FC Trailing Cable		6XV1830-3EH10			
- FC Food Cable (PE sheath)		6XV1830-0GH10			
- FC Robust Cable (PUR sheath)		6XV1830-0JH10			
- FC FRNC Cable (FRNC sheath)		6XV1830-0LH10			
- FC Underground Cable		6XV1830-3FH10			
- Festoon Cable GP (PVC sheath)		6XV1830-3GH10			
- FC Flexible Cable GP (PUR sheath)		6XV1831-2K			
Pre-assembled cables					
PROFIBUS M12 connecting cable, trailable, pre-assembled at both ends with PROFIBUS M12 connectors 180° (one end socket, one end pin)	0,3 m	6XV1830-3DE30			
	0,5 m	6XV1830-3DE50			
	1,0 m	6XV1830-3DH10			
	1,5 m	6XV1830-3DH15			
	2,0 m	6XV1830-3DH20			
	3,0 m	6XV1830-3DH30			
	5,0 m	6XV1830-3DH50			
	10,0 m	6XV1830-3DN10			
	15,0 m	6XV1830-3DN15			
PROFIBUS M12 connecting cable, trailable, pre-assembled at both end with PROFIBUS M12 connectors, angled (one end socket, one end pin)	1,5 m	6XV1830-3DH15-0SB0 ¹⁾			
	2,0 m	6XV1830-3DH20-0SB0 ¹⁾			
	3,0 m	3RK1902-1NB30			
	5,0 m	3RK1902-1NB50			
	10,0 m	3RK1902-1NC10			
	15,0 m	6XV1830-3DN15-0SB0 ¹⁾			
PROFIBUS M12 connecting cable, trailable, pre-assembled at one end with PROFIBUS M12 connector, angled (one end pin, one end open cable)	3,0 m	3RK1902-1GB30			
	5,0 m	3RK1902-1GB50			
	10,0 m	3RK1902-1GC10			
Miscellaneous					
M12 cover caps		3RX9802-0AA00			
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors 180° (pin)					
	0,3 m	6XV1870-8AE30			
	0,5 m	6XV1870-8AE50			
	1,0 m	6XV1870-8AH10			
	1,5 m	6XV1870-8AH15			
	2,0 m	6XV1870-8AH20			
	3,0 m	6XV1870-8AH30			
	5,0 m	6XV1870-8AH50			
	10,0 m	6XV1870-8AN10			
	15,0 m	6XV1870-8AN15			
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors, angled (pin)					
	0,3 m	6XV1870-8GE30			
	0,5 m	6XV1870-8GE50			
	1,0 m	6XV1870-8GH10			
	1,5 m	6XV1870-8GH15			
	2,0 m	6XV1870-8GH20			
	3,0 m	6XV1870-8GH30			
	5,0 m	6XV1870-8GH50			
	10,0 m	6XV1870-8GN10			
	15,0 m	6XV1870-8GN15			
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector, angled (one end pin, one end open cable)					
	3,0 m	3RK1902-2HB30			
	5,0 m	3RK1902-2HB50			
	10,0 m	3RK1902-2NC10			
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector 180° (pin), other end with RJ45 Plug 145°					
	2,0 m	6XV1871-5TH20			
	3,0 m	6XV1871-5TH30			
	5,0 m	6XV1871-5TH50			
	10,0 m	6XV1871-5TN10			
	15,0 m	6XV1871-5TN15			
Miscellaneous					
M12 cover caps		3RX9802-0AA00			
X1 P2R PN LAN (M12 socket)					
Non-assembled connectors					
PROFINET M12 plug, d-coded with short assembly times due to their insulation- and displacement technology method, 180°					
- 1 piece per pack		6GK1901-0DB10-6AA0			
- 8 pieces per pack		6GK1901-0DB10-6AA8			
PROFINET M12 plug, d-coded with FastConnect connecting method, 180°					
- 1 piece per pack		6GK1901-0DB20-6AA0			
- 8 pieces per pack		6GK1901-0DB20-6AA8			
PROFINET M12 plug, d-coded, angled		3RK1902-2DA00			
Non-assembled cables					
PROFINET FC cable					
- FC TP Standard Cable		6XV1840-2AH10			
- FC TP Trailing Cable		6XV1840-3AH10			
- FC TP Trailing Cable GP		6XV1870-2D			
- FC TP Marine Cable		6XV1840-4AH10			
- FC TP Torsion Cable		6XV1870-2F			
- FC TP Flexible Cable GP (PVC sheath)		6XV1870-2B			
- FC TP FRNC Cable (FRNC sheath)		6XV1871-2F			
- FC TP Food Cable (PE sheath)		6XV1871-2L			
- FC TP Festoon Cable GP (PVC sheath)		6XV1871-2S			

M12 terminating resistor for PROFIBUS DP	5 pieces	6GK1905-0EC00
X80 DC 24V IN (M8 pin)		
Non-assembled connectors		
M8 Power connector, socket insert, 4 pin		6ES7194-2AC00-0AA0
Pre-assembled cables		
Power cable M8, pre-assembled at both ends with M8 plug and M8 socket, 4 core	0,19 m	6ES7194-2LH02-1AA0
	0,3 m	6ES7194-2LH03-1AA0
	1,0 m	6ES7194-2LH10-1AA0
	2,0 m	6ES7194-2LH20-1AA0
	5,0 m	6ES7194-2LH50-1AA0
	10,0 m	6ES7194-2LN10-1AA0
	15,0 m	6ES7194-2LN15-1AA0
Power cable M8, PUR cable, pre-assembled at both ends with M8 plug and M8 socket, 4 core	0,19 m	6ES7194-2MH02-1AA0
	0,3 m	6ES7194-2MH03-1AA0
	1,0 m	6ES7194-2MH10-1AA0
	2,0 m	6ES7194-2MH20-1AA0
	5,0 m	6ES7194-2MH50-1AA0
	10,0 m	6ES7194-2MN10-1AA0
	15,0 m	6ES7194-2MN15-1AA0
Power cable M8, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2LH03-1AB0
	1,0 m	6ES7194-2LH10-1AB0
	2,0 m	6ES7194-2LH20-1AB0
	5,0 m	6ES7194-2LH50-1AB0
	10,0 m	6ES7194-2LN10-1AB0
	15,0 m	6ES7194-2LN15-1AB0
Power cable M8, PUR cable, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2MH03-1AB0
	1,0 m	6ES7194-2MH10-1AB0
	2,0 m	6ES7194-2MH20-1AB0
	5,0 m	6ES7194-2MH50-1AB0
	10,0 m	6ES7194-2MN10-1AB0
	15,0 m	6ES7194-2MN15-1AB0
Power cable M8, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2LH20-1AC0
	5,0 m	6ES7194-2LH50-1AC0
	10,0 m	6ES7194-2LN10-1AC0
	15,0 m	6ES7194-2LN15-1AC0
Power cable M8, PUR cable, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2MH20-1AC0
	5,0 m	6ES7194-2MH50-1AC0
	10,0 m	6ES7194-2MN10-1AC0
	15,0 m	6ES7194-2MN15-1AC0
X81 DC 24V OUT (M8 socket)		
Non-assembled connectors		
M8 Power connector, pin insert, 4 pin		6ES7194-2AA00-0AA0
Pre-assembled cables		
Power cable M8, pre-assembled at both ends with M8 plug and M8 socket, 4 core	0,19 m	6ES7194-2LH02-1AA0
	0,3 m	6ES7194-2LH03-1AA0
	1,0 m	6ES7194-2LH10-1AA0
	2,0 m	6ES7194-2LH20-1AA0
	5,0 m	6ES7194-2LH50-1AA0
	10,0 m	6ES7194-2LN10-1AA0
	15,0 m	6ES7194-2LN15-1AA0
Power cable M8, PUR cable, pre-assembled at both ends with M8 plug and M8 socket, 4 core	0,19 m	6ES7194-2MH02-1AA0
	0,3 m	6ES7194-2MH03-1AA0
	1,0 m	6ES7194-2MH10-1AA0
	1,0 m	6ES7194-2MH10-1AA0

Pre-assembled cables		
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors 180° (pin)	0,3 m	6XV1870-8AE30
	0,5 m	6XV1870-8AE50
	1,0 m	6XV1870-8AH10
	1,5 m	6XV1870-8AH15
	2,0 m	6XV1870-8AH20
	3,0 m	6XV1870-8AH30
	5,0 m	6XV1870-8AH50
	10,0 m	6XV1870-8AN10
15,0 m	6XV1870-8AN15	
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors, angled (pin)	0,3 m	6XV1870-8GE30
	0,5 m	6XV1870-8GE50
	1,0 m	6XV1870-8GH10
	1,5 m	6XV1870-8GH15
	2,0 m	6XV1870-8GH20
	3,0 m	6XV1870-8GH30
	5,0 m	6XV1870-8GH50
	10,0 m	6XV1870-8GN10
15,0 m	6XV1870-8GN15	
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector, angled (one end pin, one end open cable)	3,0 m	3RK1902-2HB30
	5,0 m	3RK1902-2HB50
	10,0 m	3RK1902-2NC10
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector 180° (pin), other end with RJ45 Plug 145°	2,0 m	6XV1871-5TH20
	3,0 m	6XV1871-5TH30
	5,0 m	6XV1871-5TH50
	10,0 m	6XV1871-5TN10
	15,0 m	6XV1871-5TN15
Miscellaneous		
M12 cover caps		3RX9802-0AA00
X80 DC 24V IN (M8 pin)		
Non-assembled connectors		
M8 Power connector, socket insert, 4 pin		6ES7194-2AC00-0AA0
Pre-assembled cables		
Power cable M8, pre-assembled at both ends with M8 plug and M8 socket, 4 core	0,19 m	6ES7194-2LH02-1AA0
	0,3 m	6ES7194-2LH03-1AA0
	1,0 m	6ES7194-2LH10-1AA0
	2,0 m	6ES7194-2LH20-1AA0
	5,0 m	6ES7194-2LH50-1AA0
	10,0 m	6ES7194-2LN10-1AA0
	15,0 m	6ES7194-2LN15-1AA0
	Power cable M8, PUR cable, pre-assembled at both ends with M8 plug and M8 socket, 4 core	0,19 m
0,3 m		6ES7194-2MH03-1AA0
1,0 m		6ES7194-2MH10-1AA0
2,0 m		6ES7194-2MH20-1AA0
5,0 m		6ES7194-2MH50-1AA0
10,0 m		6ES7194-2MN10-1AA0
15,0 m		6ES7194-2MN15-1AA0
Power cable M8, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2LH03-1AB0
	1,0 m	6ES7194-2LH10-1AB0
	2,0 m	6ES7194-2LH20-1AB0
	5,0 m	6ES7194-2LH50-1AB0
	10,0 m	6ES7194-2LN10-1AB0
	15,0 m	6ES7194-2LN15-1AB0

	2,0 m	6ES7194-2MH20-1AA0			
	5,0 m	6ES7194-2MH50-1AA0			
	10,0 m	6ES7194-2MN10-1AA0			
	15,0 m	6ES7194-2MN15-1AA0			
Power cable M8, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2LH03-1AB0			
	1,0 m	6ES7194-2LH10-1AB0			
	2,0 m	6ES7194-2LH20-1AB0			
	5,0 m	6ES7194-2LH50-1AB0			
	10,0 m	6ES7194-2LN10-1AB0			
	15,0 m	6ES7194-2LN15-1AB0			
Power cable M8, PUR cable, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2MH03-1AB0			
	1,0 m	6ES7194-2MH10-1AB0			
	2,0 m	6ES7194-2MH20-1AB0			
	5,0 m	6ES7194-2MH50-1AB0			
	10,0 m	6ES7194-2MN10-1AB0			
	15,0 m	6ES7194-2MN15-1AB0			
Power cable M8, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2LH20-1AC0			
	5,0 m	6ES7194-2LH50-1AC0			
	10,0 m	6ES7194-2LN10-1AC0			
	15,0 m	6ES7194-2LN15-1AC0			
Power cable M8, PUR cable, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2MH20-1AC0			
	5,0 m	6ES7194-2MH50-1AC0			
	10,0 m	6ES7194-2MN10-1AC0			
	15,0 m	6ES7194-2MN15-1AC0			
Miscellaneous					
M8 cover caps		3RK1901-1PN00			
X30 ET-CON1 (M8 socket)					
Non-assembled connectors					
M8 connector for ET-Connection, 4 pin, shield		6ES7194-2AB00-0AA0			
Pre-assembled cables					
Bus cable for ET-Connection M8, pre-assembled at both ends with 2 x M8 connectors, 4 core, shield	0,19 m	6ES7194-2LH02-0AA0			
	0,3 m	6ES7194-2LH03-0AA0			
	1,0 m	6ES7194-2LH10-0AA0			
	2,0 m	6ES7194-2LH20-0AA0			
	5,0 m	6ES7194-2LH50-0AA0			
	10,0 m	6ES7194-2LN10-0AA0			
	15,0 m	6ES7194-2LN15-0AA0			
Bus cable for ET-Connection M8, PUR cable, pre-assembled at both ends with 2 x M8 connectors, 4 core, shield	0,19 m	6ES7194-2MH02-0AA0			
	0,3 m	6ES7194-2MH03-0AA0			
	1,0 m	6ES7194-2MH10-0AA0			
	2,0 m	6ES7194-2MH20-0AA0			
	5,0 m	6ES7194-2MH50-0AA0			
	10,0 m	6ES7194-2MN10-0AA0			
	15,0 m	6ES7194-2MN15-0AA0			
Bus cable for ET-Connection M8, pre-assembled at both ends with 2 x M8 connectors angled, 4 core, shield	0,3 m	6ES7194-2LH03-0AB0			
	1,0 m	6ES7194-2LH10-0AB0			
	2,0 m	6ES7194-2LH20-0AB0			
	5,0 m	6ES7194-2LH50-0AB0			
	10,0 m	6ES7194-2LN10-0AB0			
	15,0 m	6ES7194-2LN15-0AB0			
	0,3 m	6ES7194-2MH03-1AB0			
	1,0 m	6ES7194-2MH10-1AB0			
	2,0 m	6ES7194-2MH20-1AB0			
	5,0 m	6ES7194-2MH50-1AB0			
	10,0 m	6ES7194-2MN10-1AB0			
	15,0 m	6ES7194-2MN15-1AB0			
	2,0 m	6ES7194-2LH20-1AC0			
	5,0 m	6ES7194-2LH50-1AC0			
	10,0 m	6ES7194-2LN10-1AC0			
	15,0 m	6ES7194-2LN15-1AC0			
Power cable M8, PUR cable, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2MH03-1AB0			
	1,0 m	6ES7194-2MH10-1AB0			
	2,0 m	6ES7194-2MH20-1AB0			
	5,0 m	6ES7194-2MH50-1AB0			
	10,0 m	6ES7194-2MN10-1AB0			
	15,0 m	6ES7194-2MN15-1AB0			
Power cable M8, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2LH20-1AC0			
	5,0 m	6ES7194-2LH50-1AC0			
	10,0 m	6ES7194-2LN10-1AC0			
	15,0 m	6ES7194-2LN15-1AC0			
Power cable M8, PUR cable, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2MH03-1AB0			
	1,0 m	6ES7194-2MH10-1AB0			
	2,0 m	6ES7194-2MH20-1AB0			
	5,0 m	6ES7194-2MH50-1AB0			
	10,0 m	6ES7194-2MN10-1AB0			
	15,0 m	6ES7194-2MN15-1AB0			
Power cable M8, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2LH20-1AC0			
	5,0 m	6ES7194-2LH50-1AC0			
	10,0 m	6ES7194-2LN10-1AC0			
	15,0 m	6ES7194-2LN15-1AC0			
Power cable M8, PUR cable, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2MH03-1AB0			
	1,0 m	6ES7194-2MH10-1AB0			
	2,0 m	6ES7194-2MH20-1AB0			
	5,0 m	6ES7194-2MH50-1AB0			
	10,0 m	6ES7194-2MN10-1AB0			
	15,0 m	6ES7194-2MN15-1AB0			
Power cable M8, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2LH20-1AC0			
	5,0 m	6ES7194-2LH50-1AC0			
	10,0 m	6ES7194-2LN10-1AC0			
	15,0 m	6ES7194-2LN15-1AC0			
Power cable M8, PUR cable, pre-assembled at both ends with M8 plug (angled) and M8 socket (angled), 4 core	0,3 m	6ES7194-2MH03-1AB0			
	1,0 m	6ES7194-2MH10-1AB0			
	2,0 m	6ES7194-2MH20-1AB0			
	5,0 m	6ES7194-2MH50-1AB0			
	10,0 m	6ES7194-2MN10-1AB0			
	15,0 m	6ES7194-2MN15-1AB0			
Power cable M8, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2LH20-1AC0			
	5,0 m	6ES7194-2LH50-1AC0			
	10,0 m	6ES7194-2LN10-1AC0			
	15,0 m	6ES7194-2LN15-1AC0			

	10,0 m	6ES7194-2LN10-0AB0			
	15,0 m	6ES7194-2LN15-0AB0			
Bus cable for ET-Connection M8, PUR cable, pre-assembled at both ends with 2 x M8 connectors angled, 4 core, shield	0,3 m	6ES7194-2MH03-0AB0	Power cable M8, PUR cable, pre-assembled at one end with M8 socket, 4 core	2,0 m	6ES7194-2MH20-1AC0
	1,0 m	6ES7194-2MH10-0AB0		5,0 m	6ES7194-2MH50-1AC0
	2,0 m	6ES7194-2MH20-0AB0		10,0 m	6ES7194-2MN10-1AC0
	5,0 m	6ES7194-2MH50-0AB0		15,0 m	6ES7194-2MN15-1AC0
	10,0 m	6ES7194-2MN10-0AB0			
	15,0 m	6ES7194-2MN15-0AB0			
Miscellaneous					
			M8 cover caps		3RK1901-1PN00
X30 ET-CON1 (M8 socket)					
Non-assembled connectors					
			M8 connector for ET-Connection, 4 pin, shield		6ES7194-2AB00-0AA0
Pre-assembled cables					
Bus cable for ET-Connection M8, pre-assembled at one end with M8 connector, 4 core, shield	2,0 m	6ES7194-2LH20-0AC0	Bus cable for ET-Connection M8, pre-assembled at both ends with 2 x M8 connectors, 4 core, shield	0,19 m	6ES7194-2LH02-0AA0
	5,0 m	6ES7194-2LH50-0AC0		0,3 m	6ES7194-2LH03-0AA0
	10,0 m	6ES7194-2LN10-0AC0		1,0 m	6ES7194-2LH10-0AA0
	15,0 m	6ES7194-2LN15-0AC0		2,0 m	6ES7194-2LH20-0AA0
				5,0 m	6ES7194-2LH50-0AA0
				10,0 m	6ES7194-2LN10-0AA0
			15,0 m	6ES7194-2LN15-0AA0	
Bus cable for ET-Connection M8, PUR cable, pre-assembled at one end with M8 connector, 4 core, shield	2,0 m	6ES7194-2MH20-0AC0	Bus cable for ET-Connection M8, PUR cable, pre-assembled at both ends with 2 x M8 connectors, 4 core, shield	0,19 m	6ES7194-2MH02-0AA0
	5,0 m	6ES7194-2MH50-0AC0		0,3 m	6ES7194-2MH03-0AA0
	10,0 m	6ES7194-2MN10-0AC0		1,0 m	6ES7194-2MH10-0AA0
	15,0 m	6ES7194-2MN15-0AC0		2,0 m	6ES7194-2MH20-0AA0
				5,0 m	6ES7194-2MH50-0AA0
				10,0 m	6ES7194-2MN10-0AA0
			15,0 m	6ES7194-2MN15-0AA0	
Miscellaneous					
Connection cable for ET-Connection, preassembled with 2 x M8 socket, 4 core, shielded	0,2 m	6ES7194-2LH02-0AD0			
Connection cable for ET-Connection, PUR cable, preassembled with 2 x M8 socket, 4 core, shielded	0,2 m	6ES7194-2MH02-0AD0			
M8 cover caps		3RK1901-1PN00			
X31 ET-CON2 (M8 socket)					
Non-assembled connectors					
			M8 connector for ET-Connection, 4 pin, shield		6ES7194-2AB00-0AA0
Pre-assembled cables					
Bus cable for ET-Connection M8, pre-assembled at both ends with 2 x M8 connectors, 4 core, shield	0,19 m	6ES7194-2LH02-0AA0	Bus cable for ET-Connection M8, pre-assembled at both ends with 2 x M8 connectors, angled, 4 core, shield	0,3 m	6ES7194-2LH03-0AB0
	0,3 m	6ES7194-2LH03-0AA0		1,0 m	6ES7194-2LH10-0AB0
	1,0 m	6ES7194-2LH10-0AA0		2,0 m	6ES7194-2LH20-0AB0
	2,0 m	6ES7194-2LH20-0AA0		5,0 m	6ES7194-2LH50-0AB0
	5,0 m	6ES7194-2LH50-0AA0		10,0 m	6ES7194-2LN10-0AB0
	10,0 m	6ES7194-2LN10-0AA0		15,0 m	6ES7194-2LN15-0AB0
Bus cable for ET-Connection M8, PUR cable, pre-assembled at both ends with 2 x M8 connectors, 4 core, shield	0,19 m	6ES7194-2MH02-0AA0	Bus cable for ET-Connection M8, PUR cable, pre-assembled at both ends with 2 x M8 connectors, angled, 4 core, shield	0,3 m	6ES7194-2MH03-0AB0
	0,3 m	6ES7194-2MH03-0AA0		1,0 m	6ES7194-2MH10-0AB0
	1,0 m	6ES7194-2MH10-0AA0		2,0 m	6ES7194-2MH20-0AB0
	2,0 m	6ES7194-2MH20-0AA0		5,0 m	6ES7194-2MH50-0AB0
	5,0 m	6ES7194-2MH50-0AA0		10,0 m	6ES7194-2MN10-0AB0
	10,0 m	6ES7194-2MN10-0AA0		15,0 m	6ES7194-2MN15-0AB0
Bus cable for ET-Connection M8, pre-assembled at both ends with 2 x M8 connectors angled, 4 core, shield	0,3 m	6ES7194-2LH03-0AB0	Bus cable for ET-Connection M8, pre-assembled at one end with M8 connectors, 4 core, shield	2,0 m	6ES7194-2LH20-0AC0
	1,0 m	6ES7194-2LH10-0AB0		5,0 m	6ES7194-2LH50-0AC0
	2,0 m	6ES7194-2LH20-0AB0		10,0 m	6ES7194-2LN10-0AC0
	5,0 m	6ES7194-2LH50-0AB0		15,0 m	6ES7194-2LN15-0AC0
	10,0 m	6ES7194-2LN10-0AB0			
	15,0 m	6ES7194-2LN15-0AB0			
Bus cable for ET-Connection M8, PUR cable, pre-assembled at both ends with 2 x M8 connectors angled, 4 core, shield	0,3 m	6ES7194-2MH03-0AB0	Bus cable for ET-Connection M8, PUR cable, pre-assembled at one end with M8 connectors, 4 core, shield	2,0 m	6ES7194-2MH20-0AC0
	1,0 m	6ES7194-2MH10-0AB0		5,0 m	6ES7194-2MH50-0AC0
	2,0 m	6ES7194-2MH20-0AB0		10,0 m	6ES7194-2MN10-0AC0
	5,0 m	6ES7194-2MH50-0AB0		15,0 m	6ES7194-2MN15-0AC0
	10,0 m	6ES7194-2MN10-0AB0			
	15,0 m	6ES7194-2MN15-0AB0			
Miscellaneous					
Connection cable for ET-Connection, preassembled with 2 x M8 socket, 4 core, shielded	0,2 m	6ES7194-2LH02-0AD0			
Connection cable for ET-Connection, PUR cable, preassembled with 2 x M8 socket, 4 core, shielded	0,2 m	6ES7194-2MH02-0AD0			
M8 cover caps		3RK1901-1PN00			
X31 ET-CON2 (M8 socket)					
Non-assembled connectors					

Bus cable for ET-Connection M8, pre-assembled at one end with M8 connector, 4 core, shield	2,0 m	6ES7194-2LH20-0AC0	M8 connector for ET-Connection, 4 pin, shield		6ES7194-2AB00-0AA0	
	5,0 m	6ES7194-2LH50-0AC0				
	10,0 m	6ES7194-2LN10-0AC0				
	15,0 m	6ES7194-2LN15-0AC0				
Bus cable for ET-Connection M8, PUR cable, pre-assembled at one end with M8 connector, 4 core, shield	2,0 m	6ES7194-2MH20-0AC0	Pre-assembled cables	Bus cable for ET-Connection M8, pre-assembled at both ends with 2 x M8 connectors, 4-core, shield	0,19 m	6ES7194-2LH02-0AA0
	5,0 m	6ES7194-2MH50-0AC0			0,3 m	6ES7194-2LH03-0AA0
	10,0 m	6ES7194-2MN10-0AC0			1,0 m	6ES7194-2LH10-0AA0
	15,0 m	6ES7194-2MN15-0AC0			2,0 m	6ES7194-2LH20-0AA0
Miscellaneous				5,0 m	6ES7194-2LH50-0AA0	
				10,0 m	6ES7194-2LN10-0AA0	
				15,0 m	6ES7194-2LN15-0AA0	
Connection cable for ET-Connection, preassembled with 2 x M8 socket, 4 core, shielded	0,2 m	6ES7194-2LH02-0AD0	Bus cable for ET-Connection M8, PUR cable, pre-assembled at both ends with 2 x M8 connectors, 4-core, shield	0,19 m	6ES7194-2MH02-0AA0	
Connection cable for ET-Connection, PUR cable, preassembled with 2 x M8 socket, 4 core, shielded	0,2 m	6ES7194-2MH02-0AD0			0,3 m	6ES7194-2MH03-0AA0
M8 cover caps		3RK1901-1PN00			1,0 m	6ES7194-2MH10-0AA0
					2,0 m	6ES7194-2MH20-0AA0
Universal accessories				5,0 m	6ES7194-2MH50-0AA0	
other cable length as above-mentioned		on request		10,0 m	6ES7194-2MN10-0AA0	
Stripping Tool ET-Conenction		6ES7194-2KA00-0AA0		15,0 m	6ES7194-2MN15-0AA0	
Idendification labels 10x5mm, RAL9016		6ES7194-2BA00-0AA0	Bus cable for ET-Connection M8, pre-assembled at both ends with 2 x M8 connectors, angled, 4 core, shield	0,3 m	6ES7194-2LH03-0AB0	
torque wrenches set M8/M12, variable adjustable		www.peres.de PER091			1,0 m	6ES7194-2LH10-0AB0
					2,0 m	6ES7194-2LH20-0AB0
					5,0 m	6ES7194-2LH50-0AB0
				10,0 m	6ES7194-2LN10-0AB0	
				15,0 m	6ES7194-2LN15-0AB0	
			Bus cable for ET-Connection M8, PUR cable, pre-assembled at both ends with 2 x M8 connectors, angled, 4 core, shield	0,3 m	6ES7194-2MH03-0AB0	
					1,0 m	6ES7194-2MH10-0AB0
					2,0 m	6ES7194-2MH20-0AB0
					5,0 m	6ES7194-2MH50-0AB0
				10,0 m	6ES7194-2MN10-0AB0	
				15,0 m	6ES7194-2MN15-0AB0	
			Bus cable for ET-Connection M8, pre-assembled at one end with M8 connectors, 4 core, shield	2,0 m	6ES7194-2LH20-0AC0	
					5,0 m	6ES7194-2LH50-0AC0
					10,0 m	6ES7194-2LN10-0AC0
					15,0 m	6ES7194-2LN15-0AC0
			Bus cable for ET-Connection M8, PUR cable, pre-assembled at one end with M8 connectors, 4 core, shield	2,0 m	6ES7194-2MH20-0AC0	
					5,0 m	6ES7194-2MH50-0AC0
					10,0 m	6ES7194-2MN10-0AC0
					15,0 m	6ES7194-2MN15-0AC0
Miscellaneous						
Connection cable for ET-Connection, preassembled with 2 x M8 socket, 4 core, shielded	0,2 m	6ES7194-2LH02-0AD0				
Connection cable for ET-Connection, PUR cable, preassembled with 2 x M8 socket, 4 core, shielded	0,2 m	6ES7194-2MH02-0AD0				
M8 cover caps		3RK1901-1PN00				
Universal accessories						
other cable length as above-mentioned		on request				
Stripping Tool ET-Conenction		6ES7194-2KA00-0AA0				
Idendification labels 10x5mm, RAL9016		6ES7194-2BA00-0AA0				
torque wrenches set M8/M12, variable adjustable		www.peres.de PER091				

¹⁾ Ordering with ORG-ID 10001539