



Up to 50%  
savings



# Wi-Fi 6 for industry with Access Points and Client Modules

Test one of our promotional packages SCALANCE W700 right now!

Reliable and powerful wireless connectivity with maximum data transmission rates and robust, industry-capable hardware plays a decisive role in demanding Industrie 4.0 applications such as augmented reality or remote-controlled cranes.

This also applies to, e.g., the intralogistics or transportation industry, which require the wireless connection of a large amount of mobile devices in a confined space and where industry-specific approvals are necessary. The optimal combination of Access Points SCALANCE WAM766-1 with the Client Module SCALANCE WUM763-1 and the corresponding accessories allows you to take full advantage of the benefits of Wi-Fi 6 for the industry.

## Your benefits

- Investment protection due to state-of-the-art powerful WLAN standard IEEE 802.11ax (Wi-Fi 6) with a gross data rate of 1,201 Mbps and an increased net data rate per WLAN client due to an enhanced data transmission fairness among the network participants.
- Energy-efficient operation of mobile participants thanks to a digital input/output interface (DI/DO) and sleep mode functionality. This allows applications such as AGV fleets, shuttles, and cranes to benefit from a significantly reduced power consumption.
- Industry-specific features for real-time communication or redundant, highly available communication (iFeatures iPCF-2 or iPRP) via CLP.
- Robust IP65 hardware for flexible, international use in demanding wireless industrial applications as well as extended environmental conditions.
- TCP Event Roaming enabling seamless roaming for the application by steering the clients at the right position to the right Access Point. Details at [support.industry.siemens.com/cs/ww/en/view/109815243](https://support.industry.siemens.com/cs/ww/en/view/109815243)
- International wireless approvals: [siemens.com/wireless-approvals](https://siemens.com/wireless-approvals)

When it comes to implementing demanding wireless applications with Industrial Wireless LAN reliably and future-proof in an industrial environment while simultaneously leveraging the benefits of the new WLAN standard IEEE 802.11ax (Wi-Fi 6), then SCALANCE W700 with Wi-Fi 6 is just the right option for you.

With this promotional package you can test reliable communication via Industrial Wireless LAN with Wi-Fi 6 and versatile hardware.

## Order your promotional package now!<sup>1)</sup>

|                                                                                                                                                                                                                                                                                                                                                                                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>SCALANCE W Access Point &amp; Client Module<sup>2)</sup></b><br> <ul style="list-style-type: none"><li>• 1 x SCALANCE WAM763-1</li><li>• 1 x SCALANCE WUM763-1</li><li>• 4 x ANT795-4MB IWLAN antenna</li></ul> <p><b>Article No.:</b> 6GK5763-1AL00-3KA0<br/>6GK5763-1AL00-3KB0</p> <p><b>Price:</b> please ask your sales representative</p> | <b>SCALANCE W Access Points &amp; Client Module with Accessories<sup>2)</sup></b><br> <ul style="list-style-type: none"><li>• 1 x SCALANCE WAM766-1</li><li>• 1 x SCALANCE WAM763-1</li><li>• 1 x SCALANCE WUM763-1</li><li>• 2 x ANT795-4MX IWLAN antenna</li><li>• 4 x ANT795-4MB IWLAN antenna</li><li>• 1 x IE TP Cord M12-180/RJ45-180 (X-coded)</li><li>• 1 x SCALANCE CLP 2GB W700 Client iFeatures</li><li>• 2 x SCALANCE CLP 2GB W700 AP iFeatures</li></ul> <p><b>Article No.:</b> 6GK5763-1AL00-3LA0<br/>6GK5763-1AL00-3LB0</p> <p><b>Price:</b> please ask your sales representative</p> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Further useful products

| Product name                              | Article No.        | Notes                                                                                                                                              |
|-------------------------------------------|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
| SCALANCE CLP 2GB W700 AP iFeatures        | 6GK5907-8UA00-0AA0 | Removable data storage medium for the SCALANCE W1700/WxM760 product range for upgrading with additional functions (iFeatures) in Access Point mode |
| SCALANCE CLP 2GB W700 Client iFeatures    | 6GK5907-4UA00-0AA0 | Removable data storage medium for the SCALANCE W1700/WxM760 product range for upgrading with additional functions (iFeatures) in Client mode       |
| SITOP PSU6200 24 V/1.3 A with NEC Class 2 | 6EP3331-7SB00-0AX0 | Regulated power supply input: 120 – 230 V AC (120 – 240 V DC) output: 24 V DC/1.3 A                                                                |

<sup>1)</sup> 10 promotional packages can be ordered per customer. The general terms and conditions of payment and delivery for products and services of the electrical industry apply. Prices are shown in Euros, exworks, and do not include sales tax or postage and packaging.

<sup>2)</sup> Consider country-specific approvals: [www.siemens.com/wireless-approvals](http://www.siemens.com/wireless-approvals)