

Spare part SIMATIC S7-200, CPU 224 Compact unit, DC power supply 14 DI DC/10 DO DC, 8/12 KB progr./8 KB data, PROFIBUS DP expandable



Figure similar

Supply voltage	
Rated value (DC)	
<ul style="list-style-type: none"> • 24 V DC 	Yes
Load voltage L+	
<ul style="list-style-type: none"> • Rated value (DC) 	24 V
<ul style="list-style-type: none"> • permissible range, lower limit (DC) 	20.4 V
<ul style="list-style-type: none"> • permissible range, upper limit (DC) 	28.8 V
Input current	
Inrush current, max.	12 A; at 28.8 V
from supply voltage L+, max.	700 mA; 110 mA to 700 mA, output current for expansion modules (5 V DC) 660 mA
Encoder supply	
24 V encoder supply	
<ul style="list-style-type: none"> • 24 V 	Yes; permissible range: 15.4 to 28.8 V
<ul style="list-style-type: none"> • Short-circuit protection 	Yes; electronic at 280 mA
<ul style="list-style-type: none"> • Output current, max. 	280 mA

Power loss	
Power loss, typ.	7 W
Memory	
Number of memory modules (optional)	1; pluggable memory module, content identical with integral EEPROM; can additionally store recipes, data logs and other files
Work memory	
<ul style="list-style-type: none"> integrated (for program) integrated (for data) 	12 kbyte; 8 KB with active run-time edit 8 kbyte
Backup	
<ul style="list-style-type: none"> present 	Yes; Program: Entire program maintenance-free on integral EEPROM, programmable via CPU; data: Entire DB 1 loaded from PG/PC maintenance-free on integral EEPROM, current values of DB 1 in RAM, retentive memory bits, timers, counters, etc. maintenance-free via high-performance capacitor; optional battery for long-term buffering
Battery	
Backup battery	
<ul style="list-style-type: none"> Backup time, max. 	100 h; (min. 70 h at 40 °C); 200 days (typ.) with optional battery module
CPU processing times	
for bit operations, max.	0.22 μs
Counters, timers and their retentivity	
S7 counter	
<ul style="list-style-type: none"> Number 	256
Retentivity	
— adjustable	Yes; via high-performance capacitor or battery
— lower limit	1
— upper limit	256
Counting range	
— lower limit	0
— upper limit	32 767
S7 times	
<ul style="list-style-type: none"> Number 	256
Retentivity	
— adjustable	Yes; via high-performance capacitor or battery
— upper limit	64
Time range	
— lower limit	1 ms
— upper limit	54 min; 4 timers: 1 ms to 30 s; 16 timers: 10 ms to 5 min; 236 timers: 100 ms to 54 min
Data areas and their retentivity	

Flag	
• Number, max.	32 byte
• of which retentive with battery	0 to 255, via high-performance capacitor or battery, adjustable
• of which retentive without battery	0 to 112 in EEPROM, adjustable

Hardware configuration

Number of expansion units, max.	7; Only expansion modules of the S7-22x series can be used. Due to the limited output current, the use of expansion modules may be limited.
connectable programming devices/PCs	SIMATIC PG/PC, standard PC

Expansion modules

• Analog inputs/outputs, max.	35; max. 28 inputs and 7 outputs (EM) or max. 0 inputs and 14 outputs (EM)
• Digital inputs/outputs, max.	168; max. 94 inputs and 74 outputs (CPU + EM)
• AS-Interface inputs/outputs, max.	62; AS-Interface A/B slaves (CP 243-2)

Digital inputs

Number of digital inputs	14
Source/sink input	Yes; optionally, per group

Input voltage

• Rated value (DC)	24 V
• for signal "0"	0 to 5 V
• for signal "1"	min. 15 V

Input current

• for signal "1", typ.	2.5 mA
------------------------	--------

Input delay (for rated value of input voltage)

for standard inputs	
— parameterizable	Yes; all
— at "0" to "1", min.	0.2 ms
— at "0" to "1", max.	12.8 ms

for interrupt inputs

— parameterizable	Yes; I 0.0 to I 0.3
-------------------	---------------------

for technological functions

— parameterizable	Yes; (E 0.0 to E 1.5) 30 kHz
-------------------	------------------------------

Cable length

• shielded, max.	500 m; Standard input: 500 m, high-speed counters: 50 m
• unshielded, max.	300 m; not for high-speed signals

Digital outputs

Number of digital outputs	10; Transistor
Short-circuit protection	No; to be provided externally

Limitation of inductive shutdown voltage to	1 W
---	-----

Switching capacity of the outputs

• with resistive load, max.	0.75 A
-----------------------------	--------

• on lamp load, max.	5 W
Output voltage	
• for signal "1", min.	20 V DC
Output current	
• for signal "1" rated value	750 mA
• for signal "0" residual current, max.	10 μ A
Output delay with resistive load	
• "0" to "1", max.	15 μ s; of the standard outputs, max. (Q 0.2 to Q 1.1) 2 μ s; of the pulse outputs, max. (Q 0.0 to Q 0.1) 2 μ s
• "1" to "0", max.	130 μ s; of the standard outputs, max. (Q 0.2 to Q 1.1) 10 μ s; of the pulse outputs, max. (Q 0.0 to Q 0.1) 10 μ s
Parallel switching of two outputs	
• for uprating	Yes
Switching frequency	
• of the pulse outputs, with resistive load, max.	20 kHz; Q0.0 to Q0.1
Total current of the outputs (per group)	
all mounting positions	
— up to 40 °C, max.	6 A
horizontal installation	
— up to 55 °C, max.	6 A
Relay outputs	
• Number of relay outputs	0
• Number of relay outputs, integrated	0
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m
Analog inputs	
Number of analog potentiometers	2; Analog potentiometer; resolution 8 bit
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	1 mA
1. Interface	
Interface type	Integrated RS 485 interface
Physics	RS 485
Protocols	
• MPI	Yes; As MPI slave for data exchange with MPI masters (S7-300/S7-400 CPUs, OPs, TDs, Push Button Panels); S7-200-internal CPU/CPU communication is possible in the MPI network with restrictions; transmission rates: 19.2/187.5 kbit/s

- PPI Yes; with PPI protocol for program functions, HMI functions (TD 200, OP), S7-200-internal CPU/CPU communication ; transmission rates 9.6/19.2/187.5 kbit/s
- serial data exchange Yes; As freely programmable interface with interrupt facility for serial data exchange with third-party devices with ASCII protocol transfer rates: 1.2 / 2.4 / 4.8 / 9.6 / 19.2 / 38.4 / 57.6 / 115.2 kbps; the PC/PPI cable can also be used as RS 232/RS 485 converter

MPI	
• Transmission rate, min.	19.2 kbit/s
• Transmission rate, max.	187.5 kbit/s

Integrated Functions

Number of counters	6; High-speed counters (30 kHz each), 32 bit (incl. sign), can be used as up/down counters or for connecting 2 incremental encoders with 2 pulse trains offset by 90° (max. 20 kHz (A/B counters)); parameterizable enable and reset input; interrupt facilities (incl. call of subroutine with any content) when the setpoint is reached; reversal in counting direction, etc.
Counting frequency (counter) max.	30 kHz
Number of alarm inputs	4; 4 rising edges and/or 4 falling edges
Number of pulse outputs	2; High-speed outputs, 20 kHz, with interrupt option; pulse-width and frequency modulation option
Limit frequency (pulse)	20 kHz

Potential separation

Potential separation digital inputs	
• between the channels	Yes
• between the channels, in groups of	6 and 8
Potential separation digital outputs	
• between the channels	Yes; Optocoupler
• between the channels, in groups of	5

Permissible potential difference

between different circuits	500 V DC between 24 V DC and 5 V DC
----------------------------	-------------------------------------

Degree and class of protection

Degree of protection acc. to EN 60529	
• IP20	Yes

Ambient conditions

Ambient temperature during operation	
• horizontal installation, min.	0 °C
• horizontal installation, max.	55 °C
• vertical installation, min.	0 °C
• vertical installation, max.	45 °C
Air pressure acc. to IEC 60068-2-13	
• permissible range, lower limit	860 hPa

• permissible range, upper limit	1 080 hPa
Relative humidity	
• Operation, min.	5 %
• Operation, max.	95 %; RH class 2 in accordance with IEC 1131-2
Configuration	
Programming	
• Command set	Bit logic instructions, compare instructions, timer instructions, counter instructions, clock instructions, transmissions instructions, table instructions, logic instructions, shift and rotate instructions, conversion instructions, program control instructions, interrupt and communications instructions, logic stack instructions, integer maths, floating-point math instructions, numerical functions
• Program processing	free cycle (OB 1), interrupt-controller, time-controlled (1 to 255 ms)
• Program organization	1 OB, 1 DB, 1 SDB subroutines with/without parameter transfer
• Number of subroutines, max.	64
Programming language	
— LAD	Yes
— FBD	Yes
— STL	Yes
Know-how protection	
• User program protection/password protection	Yes; 3-stage password protection
Connection method	
Plug-in I/O terminals	Yes
Dimensions	
Width	120.5 mm
Height	80 mm
Depth	62 mm
Weights	
Weight, approx.	360 g
last modified:	10/22/2019