

SIMATIC S7-300, Digital output SM 322, isolated, 32 DO, 24 V DC, 0.5A, 1x 40-pole, Total current 4 A/group (16 A/module)



Supply voltage

Load voltage L+

• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V

Input current

from load voltage L+ (without load), max.	160 mA
from backplane bus 5 V DC, max.	110 mA

Power loss

Power loss, typ.	6.6 W
------------------	-------

Digital outputs

Number of digital outputs	32
Limitation of inductive shutdown voltage to	L+ (-53 V)

Switching capacity of the outputs

• on lamp load, max.	5 W
----------------------	-----

Load resistance range

• lower limit	48 Ω
---------------	------

• upper limit	4 kΩ
Output voltage	
• for signal "1", min.	L+ (-0.8 V)
Output current	
• for signal "1" rated value	0.5 A
• for signal "1" minimum load current	5 mA
• for signal "0" residual current, max.	0.5 mA
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	0.5 Hz
• on lamp load, max.	10 Hz
Total current of the outputs (per group)	
horizontal installation	
— up to 40 °C, max.	4 A
— up to 60 °C, max.	3 A
vertical installation	
— up to 40 °C, max.	2 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Interrupts/diagnostics/status information	
Diagnostics function	No
Alarms	
• Diagnostic alarm	No
Diagnostic messages	
• Wire-break	No
• Short-circuit	No
• missing load voltage	No
Diagnostics indication LED	
• Rated load voltage PWR (green)	No
• Fuse OK FSG (green)	No
• Group error SF (red)	No
• Status indicator digital output (green)	Yes; per channel
• Channel fault indicator F (red)	No
Potential separation	
Potential separation digital outputs	
• between the channels	Yes
• between the channels, in groups of	8
• between the channels and backplane bus	Yes; Optocoupler
Isolation	
Isolation tested with	500 V DC

Connection method	
required front connector	40-pin
Dimensions	
Width	40 mm
Height	125 mm
Depth	120 mm
Weights	
Weight, approx.	260 g
last modified:	08/16/2019